

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P887020

Luminaire Tested: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K

Issue Date: 7/9/2024

Test Information

Test Method: LM-79-2019
Report Number: P887020
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/9/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K
Description: 4IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1455.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.64
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P887020
CATALOG NUMBER: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P887020

CATALOG NUMBER: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96				96															
2	110	106	103	100	108	105	102	99	101	99	97	99	97	95	96	94	93	92				92															
3	106	101	97	94	104	100	96	93	97	94	92	95	92	90	93	91	89	88				88															
4	102	96	92	89	101	95	91	88	93	90	87	91	88	86	90	87	85	84				84															
5	99	92	87	84	97	91	87	84	89	86	83	88	85	82	86	84	81	80				80															
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77				77															
7	92	84	80	76	90	84	79	76	83	79	76	81	78	75	80	77	75	74				74															
8	88	81	76	73	87	80	76	73	79	75	73	79	75	72	78	74	72	71				71															
9	85	78	73	70	84	77	73	70	77	72	70	76	72	69	75	72	69	68				68															
10	83	75	70	67	82	74	70	67	74	70	67	73	69	67	72	69	67	66				66															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402452
5°	392598
10°	356432
15°	305553
20°	231664
25°	129823
30°	50847
35°	8583
40°	1610
45°	174
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 174 cd/sqm



TEST NUMBER: P887020

CATALOG NUMBER: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	292.0	20.1
10°-20°	654.0	44.9
20°-30°	444.5	30.5
30°-40°	62.6	4.3
40°-50°	1.8	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1390.5	95.6
0°-40°	1453.2	99.9
0°-60°	1455.0	100.0
0°-90°	1455.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1455.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3263	
5°	3171	292
15°	2393	654
25°	954	444
35°	57	63
45°	1	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P887020

CATALOG NUMBER: ML412LSFL9FS1E-TIR4D40FL-TL4RDMB-1200LM-2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3262.8
2.5°	3249.8
5°	3170.8
7.5°	3028.8
10°	2845.8
12.5°	2634.8
15°	2392.8
17.5°	2112.9
20°	1764.9
22.5°	1351.9
25°	953.9
27.5°	640.0
30°	357.0
32.5°	158.0
35°	57.0
37.5°	25.0
40°	10.0
42.5°	4.0
45°	1.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)