

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P303279

Luminaire Tested: **BLD4089BLE40AWH-3500K**

Test Date: 06/19/19

Test Information

Test Method: LM-41-14
Report Number: P303279
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1906-357-1)
Test Lab: INNOVATION CENTER(G3)
Test Date: 06/19/19
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: BLD4089BLE40AWH-3500K
Description: 4" SMART SURFACE MOUNT DOWNLIGHT 3500K
Light Source: (40) 90 CRI LEDS
Ballast/Driver: ELECTRICAL DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 820.3 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.38
Luminous Opening: Vertical Cylinder (Dia: 0.33' x H: 0.08')
CIE Type: Direct

Input Watts (W): 9.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303279
CATALOG NUMBER: BLD4089BLE40AWH-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303279

CATALOG NUMBER: BLD4089BLE40AWH-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	110	110	110		105	105	105		100	100	100	98
1	107	101	96	92	104	99	94	90	94	90	87		90	87	84		86	83	81	79
2	96	87	80	74	94	85	79	73	81	76	71		78	73	69		75	71	67	65
3	88	76	68	61	85	75	67	60	71	64	59		68	62	57		65	60	56	54
4	80	67	58	51	78	66	57	51	63	56	50		61	54	49		58	53	48	46
5	74	60	51	44	71	59	50	44	57	49	43		54	48	42		52	46	42	39
6	68	54	45	38	66	53	44	38	51	43	37		49	42	37		47	41	36	34
7	63	49	40	34	61	48	40	33	46	39	33		45	38	33		43	37	32	30
8	59	45	36	30	57	44	36	30	42	35	29		41	34	29		40	33	29	27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	28	24		34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32119
5°	31248
10°	30288
15°	29462
20°	28514
25°	27541
30°	26518
35°	25415
40°	24310
45°	23195
50°	21883
55°	20579
60°	19273
65°	17727
70°	16180
75°	14833
80°	13192
85°	11625



TEST NUMBER: P303279

CATALOG NUMBER: BLD4089BLE40AWH-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	3.0
10°-20°	70.6	8.6
20°-30°	107.0	13.0
30°-40°	129.2	15.8
40°-50°	135.0	16.5
50°-60°	124.6	15.2
60°-70°	101.3	12.4
70°-80°	71.9	8.8
80°-90°	41.5	5.1
90°-100°	13.8	1.7
100°-110°	0.7	0.1
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.3	24.7
0°-40°	331.5	40.4
0°-60°	591.1	72.1
0°-90°	805.9	98.2
90°-120°	14.5	1.8
90°-150°	14.5	1.8
90°-180°	14.0	1.7
0°-180°	820.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	259	25
15°	250	71
25°	232	107
35°	206	129
45°	175	135
55°	139	125
65°	102	101
75°	68	72
85°	38	34
90°	24	13
95°	12	8
105°	0	1
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P303279

CATALOG NUMBER: BLD4089BLE40AWH-3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	260.4
2.5°	260.4
5°	259.4
7.5°	257.4
10°	255.4
12.5°	253.4
15°	250.4
17.5°	246.4
20°	242.4
22.5°	237.4
25°	232.4
27.5°	226.4
30°	220.4
32.5°	213.4
35°	206.4
37.5°	199.3
40°	191.3
42.5°	183.3
45°	175.3
47.5°	166.3
50°	157.3
52.5°	148.3
55°	139.2
57.5°	130.2
60°	121.2
62.5°	111.2
65°	102.2
67.5°	93.2
70°	84.1
72.5°	76.1
75°	68.1
77.5°	60.1
80°	52.1
82.5°	45.1
85°	38.1
87.5°	31.1
90°	24.0
92.5°	18.0
95°	12.0
97.5°	7.0
100°	3.0
102.5°	1.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P303279

CATALOG NUMBER: BLD4089BLE40AWH-3500K

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)