

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P175360

Luminaire Tested: **RL460WH830PK**

Test Date: 04/09/15

Test Information

Test Method: LM-41-14
Report Number: P175360
Test Lab: INNOVATION CENTER-P2
Test Date: 04/09/15
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL460WH830PK
Description: HALO RL460 - 4IN RECESSED -HV LED FIXTURE
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25991)
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 587.3 lumens
Efficiency: N/A
Efficacy: 81.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.24
Luminous Opening: Vertical Cylinder (Dia: 0.29' x H: 0.1')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175360
CATALOG NUMBER: RL460WH830PK

Luminous Intensity Polar Plot





TEST NUMBER: P175360

CATALOG NUMBER: RL460WH830PK

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	106	103	100	108	104	101	98	100	97	95		96	94	92		93	91	89	87
2	102	95	89	84	99	93	88	83	90	85	81		86	83	79		83	80	78	76
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75	71	68	66
4	87	76	68	62	85	75	68	62	72	66	61		70	65	60		68	63	60	58
5	80	69	61	55	78	68	60	54	66	59	54		64	58	53		62	57	53	51
6	75	63	54	48	73	62	54	48	60	53	48		58	52	47		57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43		53	47	43		52	47	42	40
8	65	52	45	39	64	52	44	39	50	44	39		49	43	39		48	43	38	37
9	61	48	41	35	60	48	40	35	47	40	35		46	39	35		45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32		42	36	32		42	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45174
5°	43522
10°	41544
15°	39675
20°	37428
25°	34915
30°	32361
35°	29568
40°	26460
45°	22934
50°	19157
55°	15208
60°	11467
65°	8072
70°	5226
75°	3693
80°	2856
85°	1512



TEST NUMBER: P175360

CATALOG NUMBER: RL460WH830PK

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	4.5
10°-20°	74.7	12.7
20°-30°	108.7	18.5
30°-40°	122.5	20.9
40°-50°	111.5	19.0
50°-60°	79.2	13.5
60°-70°	41.3	7.0
70°-80°	17.5	3.0
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	209.9	35.7
0°-40°	332.5	56.6
0°-60°	523.1	89.1
0°-90°	587.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	587.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	279	26
15°	266	75
25°	236	109
35°	196	123
45°	145	111
55°	88	79
65°	41	41
75°	16	17
85°	5	5
90°	0	



TEST NUMBER: P175360

CATALOG NUMBER: RL460WH830PK

CANDELA DISTRIBUTION (FULL):

	0°
0°	280.4
2.5°	279.4
5°	279.4
7.5°	277.4
10°	273.5
12.5°	269.6
15°	265.7
17.5°	259.8
20°	253.0
22.5°	244.2
25°	236.4
27.5°	227.6
30°	217.8
32.5°	208.1
35°	196.3
37.5°	184.6
40°	171.9
42.5°	159.2
45°	144.6
47.5°	130.9
50°	116.2
52.5°	102.6
55°	87.9
57.5°	75.2
60°	62.5
62.5°	50.8
65°	41.0
67.5°	32.2
70°	24.4
72.5°	19.5
75°	15.6
77.5°	13.7
80°	10.7
82.5°	7.8
85°	4.9
87.5°	2.0
90°	0.0

(END OF REPORT)