

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P123689

Luminaire Tested: **EL406927-TL411WB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P123689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13981)
Test Lab: INNOVATION CENTER-P1
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: EL406927-TL411WB
Description: HALO 4-INCH RECESSED LED DOWNLIGHT
WHITE BAFFLE, DIFFUSE DROP LENS AND WHITE TRIM RING
Light Source: (1)SURFACE MOUNT LED, 2700K CCT, 90CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 630.0 lumens
Efficiency: N/A
Efficacy: 48.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.2
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P123689
CATALOG NUMBER: EL406927-TL411WB

Luminous Intensity Polar Plot





TEST NUMBER: P123689

CATALOG NUMBER: EL406927-TL411WB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	91	87	84		88	85	82		85	83	80	78
3	96	87	81	75	94	86	80	75	83	78	73		80	76	72		78	74	71	69
4	89	79	72	66	87	78	71	66	76	70	65		73	68	64		71	67	63	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52		62	56	52		61	55	51	50
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56	51	47	45
8	68	56	49	43	67	55	48	43	54	48	43		53	47	43		52	47	43	41
9	64	52	45	40	63	51	44	40	50	44	39		49	44	39		48	43	39	38
10	60	48	41	37	59	48	41	36	47	41	36		46	40	36		45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77494
5°	77592
10°	77175
15°	76028
20°	74300
25°	72077
30°	69276
35°	65156
40°	57966
45°	44377
50°	29236
55°	19727
60°	17060
65°	16655
70°	16221
75°	14827
80°	13512
85°	9812



TEST NUMBER: P123689

CATALOG NUMBER: EL406927-TL411WB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.5	5.3
10°-20°	94.2	15.0
20°-30°	137.0	21.7
30°-40°	150.9	24.0
40°-50°	109.8	17.4
50°-60°	49.6	7.9
60°-70°	31.8	5.0
70°-80°	18.6	3.0
80°-90°	4.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.7	42.0
0°-40°	415.6	66.0
0°-60°	574.9	91.3
0°-90°	630.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	630.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	353	
5°	352	33
15°	335	94
25°	298	137
35°	243	151
45°	143	110
55°	52	50
65°	32	32
75°	18	19
85°	4	5
90°	0	



TEST NUMBER: P123689

CATALOG NUMBER: EL406927-TL411WB

CANDELA DISTRIBUTION (FULL):

	0°
0°	353.4
2.5°	353.4
5°	352.5
7.5°	350.5
10°	346.6
12.5°	340.8
15°	334.9
17.5°	327.1
20°	318.4
22.5°	308.6
25°	297.9
27.5°	286.3
30°	273.6
32.5°	260.0
35°	243.4
37.5°	224.9
40°	202.5
42.5°	174.3
45°	143.1
47.5°	112.0
50°	85.7
52.5°	65.2
55°	51.6
57.5°	43.8
60°	38.9
62.5°	35.1
65°	32.1
67.5°	29.2
70°	25.3
72.5°	21.4
75°	17.5
77.5°	13.6
80°	10.7
82.5°	6.8
85°	3.9
87.5°	1.0
90°	0.0

(END OF REPORT)