

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P123670

Luminaire Tested: **EL406930-TL410SC**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P123670
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13976)
Test Lab: INNOVATION CENTER-P1
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: EL406930-TL410SC
Description: HALO 4-INCH RECESSED LED DOWNLIGHT
SPECULAR REFLECTOR, DIFFUSE DROP LENS AND WHITE TRIM RING
Light Source: (1)SURFACE MOUNT LED, 3000K CCT, 90CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 720.0 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.25
Luminous Opening: Circular (Dia: 0.29' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P123670
CATALOG NUMBER: EL406930-TL410SC

Luminous Intensity Polar Plot





TEST NUMBER: P123670

CATALOG NUMBER: EL406930-TL410SC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96	94	93	91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82	78	76	74
4	92	83	76	71	90	82	76	71	79	74	70		77	73	69		75	71	68	66
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70	65	62	60
6	80	70	62	57	79	69	62	57	67	61	57		66	60	56		64	60	56	54
7	75	64	57	52	74	63	57	52	62	56	51		61	55	51		59	55	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43		52	47	43		51	46	43	41
10	62	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63926
5°	64170
10°	65599
15°	67766
20°	69846
25°	69770
30°	67100
35°	61558
40°	53544
45°	41329
50°	26843
55°	14297
60°	4801
65°	1601
70°	518
75°	685
80°	0
85°	0



TEST NUMBER: P123670

CATALOG NUMBER: EL406930-TL410SC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.0	5.3
10°-20°	115.1	16.0
20°-30°	179.6	24.9
30°-40°	194.1	27.0
40°-50°	138.8	19.3
50°-60°	48.4	6.7
60°-70°	5.3	0.7
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.7	46.2
0°-40°	526.8	73.2
0°-60°	714.0	99.2
0°-90°	720.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	397	
5°	397	38
15°	406	115
25°	392	180
35°	313	194
45°	181	139
55°	51	48
65°	4	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P123670

CATALOG NUMBER: EL406930-TL410SC

CANDELA DISTRIBUTION (FULL):

	0°
0°	396.8
2.5°	396.8
5°	396.8
7.5°	398.9
10°	401.0
12.5°	403.1
15°	406.3
17.5°	408.4
20°	407.4
22.5°	402.1
25°	392.5
27.5°	378.7
30°	360.7
32.5°	338.4
35°	313.0
37.5°	285.4
40°	254.6
42.5°	219.6
45°	181.4
47.5°	143.2
50°	107.1
52.5°	76.4
55°	50.9
57.5°	30.8
60°	14.9
62.5°	7.4
65°	4.2
67.5°	2.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)