

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P123683

Luminaire Tested: **EL406935-TL410WH**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P123683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13979)
Test Lab: INNOVATION CENTER-P1
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: EL406935-TL410WH
Description: HALO 4-INCH RECESSED LED DOWNLIGHT
WHITE REFLECTOR, DIFFUSE DROP LENS AND WHITE TRIM RING
Light Source: (1)SURFACE MOUNT LED, 3500K CCT, 90CRI
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 700.0 lumens
Efficiency: N/A
Efficacy: 53.8 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.19
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P123683
CATALOG NUMBER: EL406935-TL410WH

Luminous Intensity Polar Plot





TEST NUMBER: P123683

CATALOG NUMBER: EL406935-TL410WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	98	96	97	95	93	94	92	91	89
2	103	97	91	86	101	95	90	85	91	87	84	88	85	82	85	82	80	78
3	96	87	80	75	94	86	79	75	83	78	73	80	76	72	78	74	71	69
4	89	79	72	66	87	78	71	66	75	70	65	73	68	64	71	67	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	77	66	58	53	76	65	58	53	63	57	52	62	56	52	60	55	51	49
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	47	45
8	68	56	48	43	66	55	48	43	54	48	43	53	47	43	52	46	42	41
9	64	52	45	40	63	51	44	39	50	44	39	49	43	39	48	43	39	37
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86813
5°	86661
10°	85970
15°	84223
20°	82024
25°	79287
30°	75860
35°	71233
40°	63462
45°	49990
50°	34319
55°	23168
60°	19428
65°	19094
70°	18016
75°	16521
80°	15027
85°	10819



TEST NUMBER: P123683

CATALOG NUMBER: EL406935-TL410WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	5.3
10°-20°	104.3	14.9
20°-30°	150.6	21.5
30°-40°	164.8	23.5
40°-50°	123.3	17.6
50°-60°	57.8	8.3
60°-70°	36.0	5.1
70°-80°	20.7	3.0
80°-90°	5.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.3	41.8
0°-40°	457.1	65.3
0°-60°	638.2	91.2
0°-90°	700.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	396	
5°	394	37
15°	371	104
25°	328	151
35°	266	165
45°	161	123
55°	61	58
65°	37	36
75°	20	21
85°	4	5
90°	0	



TEST NUMBER: P123683

CATALOG NUMBER: EL406935-TL410WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	395.9
2.5°	395.9
5°	393.7
7.5°	390.4
10°	386.1
12.5°	378.5
15°	371.0
17.5°	361.2
20°	351.5
22.5°	339.6
25°	327.7
27.5°	314.7
30°	299.6
32.5°	283.4
35°	266.1
37.5°	245.5
40°	221.7
42.5°	192.5
45°	161.2
47.5°	128.7
50°	100.6
52.5°	76.8
55°	60.6
57.5°	49.8
60°	44.3
62.5°	40.0
65°	36.8
67.5°	32.4
70°	28.1
72.5°	23.8
75°	19.5
77.5°	15.1
80°	11.9
82.5°	7.6
85°	4.3
87.5°	1.1
90°	0.0

(END OF REPORT)