

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640483

Luminaire Tested: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K
Description: ML56 RR, 55D TIR OPTIC, 5" DEADFRONT TRIM
Light Source: (1) D2W SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1132.7 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.89
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 11.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640483
CATALOG NUMBER: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P640483

CATALOG NUMBER: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93																			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85																			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78																			
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72																			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	67																			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62																			
7	81	71	64	60	79	70	64	60	69	63	59	68	63	59	66	62	59	57																			
8	76	66	60	56	75	66	60	55	65	59	55	64	59	55	63	58	55	53																			
9	73	62	56	52	71	62	56	52	61	55	51	60	55	51	59	54	51	50																			
10	69	59	53	48	68	58	52	48	57	52	48	57	52	48	56	51	48	47																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94034
5°	90099
10°	85433
15°	80704
20°	72843
25°	61624
30°	50134
35°	39164
40°	29266
45°	19269
50°	9002
55°	3730
60°	2210
65°	1308
70°	923
75°	915
80°	909
85°	906

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19269 cd/sqm



TEST NUMBER: P640483

CATALOG NUMBER: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	9.4
10°-20°	274.6	24.2
20°-30°	323.4	28.6
30°-40°	254.8	22.5
40°-50°	132.0	11.7
50°-60°	29.4	2.6
60°-70°	7.6	0.7
70°-80°	3.2	0.3
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	704.4	62.2
0°-40°	959.2	84.7
0°-60°	1120.5	98.9
0°-90°	1132.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1191	
5°	1137	106
15°	988	275
25°	708	323
35°	406	255
45°	173	132
55°	27	29
65°	7	8
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P640483

CATALOG NUMBER: ML5609LSWFL55D2W1E - 591WB - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1191.2
2.5°	1176.2
5°	1137.0
7.5°	1098.9
10°	1065.8
12.5°	1028.6
15°	987.5
17.5°	932.3
20°	867.1
22.5°	791.8
25°	707.5
27.5°	625.2
30°	550.0
32.5°	476.7
35°	406.4
37.5°	343.2
40°	284.0
42.5°	227.8
45°	172.6
47.5°	114.4
50°	73.3
52.5°	44.2
55°	27.1
57.5°	18.1
60°	14.0
62.5°	10.0
65°	7.0
67.5°	5.0
70°	4.0
72.5°	3.0
75°	3.0
77.5°	3.0
80°	2.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)