

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: io LED

Report Number: A1913422B001

Luminaire Tested: **N/A**

Issue Date: 2019-08-14

Test Information

Test Method: LM-79-08
Report Number: A1913422B001
Test Lab: N/A
Issue Date: 2019-08-14
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: N/A
Description: LCR4129FSE010MW*
Light Source: N/A
N/A
Ballast/Driver: N/A
N/A

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1277.5 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.22 / 1.31
Luminous Opening: Point Source (0m x 0m x 0m)
CIE Type: Direct

Input Watts (W): 13.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: A1913422B001
CATALOG NUMBER: N/A

Luminous Intensity Polar Plot





TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76
3	94	85	77	72	91	83	76	71	80	74	70	77	73	69	75	71	67	65
4	86	76	68	62	84	74	67	61	72	66	60	70	64	60	68	63	59	57
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	59	47	39	34	46	39	34	44	38	34	43	38	34	32
10	56	44	36	31	55	43	36	31	42	35	31	41	35	31	40	35	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	Luminaire represents a point source (luminous area is zero).			
5°	No luminance values can be calculated.			
10°				
15°				
20°				
25°				
30°				
35°				
40°				
45°				
50°				
55°				
60°				
65°				
70°				
75°				
80°				
85°				



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	4.1
10°-20°	149.4	11.7
20°-30°	224.3	17.6
30°-40°	265.0	20.7
40°-50°	256.2	20.1
50°-60°	197.6	15.5
60°-70°	102.2	8.0
70°-80°	24.9	1.9
80°-90°	4.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.3	0.0
160°-170°	0.3	0.0
170°-180°	0.1	0.0
0°-30°	426.1	33.4
0°-40°	691.2	54.1
0°-60°	1145.0	89.6
0°-90°	1276.6	99.9
90°-120°	0.0	0.0
90°-150°	0.2	0.0
90°-180°	1.0	0.1
0°-180°	1277.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	560	560	560	560	560	
5°	557	554	556	552	557	53
15°	536	533	534	528	536	151
25°	492	492	491	486	492	227
35°	430	431	428	423	430	268
45°	334	340	337	328	334	257
55°	223	228	223	217	223	198
65°	94	111	97	98	94	94
75°	17	22	18	20	17	19
85°	1	5	1	4	1	2
90°	0	0	0	0	0	0
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	1	0	1	0	1	0
165°	1	1	1	1	1	0
175°	1	1	1	1	1	0
180°	1	1	1	1	1	



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	559.6	559.6	559.6	559.6	559.6	559.6	559.6	559.6	559.6	559.6	559.6
0.5°	558.3	556.4	552.6	553.8	556.8	554.8	554.0	550.8	559.3	557.6	554.9
1°	558.9	554.8	551.8	553.9	553.8	555.8	555.6	551.5	558.2	555.0	552.2
1.5°	556.7	556.7	554.7	557.3	555.9	554.9	555.0	552.8	557.0	553.8	550.6
2°	559.6	556.2	555.2	554.5	556.7	555.2	551.8	550.6	558.3	554.0	553.2
2.5°	560.6	552.6	556.3	553.4	555.1	556.8	553.2	549.9	557.4	554.9	551.6
3°	558.5	553.0	553.4	554.3	554.8	554.4	559.4	550.3	559.2	554.0	555.0
3.5°	557.0	553.4	551.7	552.5	557.6	552.4	553.6	549.8	559.6	552.4	554.6
4°	559.1	556.2	557.2	552.4	556.0	555.9	553.6	550.5	553.8	548.7	548.8
4.5°	557.9	554.8	552.8	557.8	556.3	554.5	553.6	550.2	554.0	548.6	552.5
5°	557.2	552.8	555.5	556.4	553.8	553.8	550.7	547.9	556.1	549.5	551.9
5.5°	556.5	554.7	549.9	547.4	552.8	552.6	549.4	548.4	554.8	550.7	550.4
6°	555.2	551.1	557.4	547.2	552.7	551.0	551.9	547.8	555.3	548.6	550.8
6.5°	555.5	547.4	550.2	546.4	552.4	550.2	548.2	547.8	554.0	546.6	549.3
7°	553.7	548.2	551.2	548.2	551.2	553.1	548.4	546.7	556.6	548.5	548.0
7.5°	554.0	552.5	548.2	549.8	551.8	548.0	549.3	546.3	556.2	545.6	547.8
8°	552.5	550.4	549.1	542.7	551.0	548.4	548.2	544.5	553.8	545.1	546.4
8.5°	552.7	551.0	545.0	545.8	548.9	549.6	545.4	542.7	549.8	547.3	548.2
9°	553.0	542.9	542.4	549.3	546.2	547.3	547.5	543.4	549.9	545.3	544.2
9.5°	548.7	544.0	544.5	546.9	546.5	544.9	545.8	543.4	547.9	544.7	544.2
10°	547.0	546.2	544.8	547.3	543.8	545.9	538.3	541.8	545.3	542.7	539.5
10.5°	545.8	542.7	543.3	541.8	545.5	542.8	541.3	539.3	546.9	541.5	536.5
11°	544.4	542.5	542.3	542.9	544.6	542.6	541.8	538.3	545.3	540.0	537.8
11.5°	543.9	539.5	541.0	540.0	541.4	540.3	540.8	536.2	543.2	540.5	538.9
12°	543.2	540.1	540.4	542.2	540.3	537.9	536.1	536.7	542.2	539.1	536.7
12.5°	540.8	539.5	538.4	539.3	540.6	538.8	537.4	535.4	540.6	534.1	536.1
13°	539.4	537.1	534.3	537.6	538.4	536.5	533.4	533.5	540.9	532.7	532.4
13.5°	539.0	535.5	532.7	536.6	537.4	536.4	532.4	531.8	540.7	531.8	530.2
14°	538.7	531.6	532.5	536.2	537.0	536.0	532.7	529.9	536.4	532.8	530.8
14.5°	533.9	531.4	533.7	534.2	534.3	532.8	533.8	529.2	535.0	529.9	529.7
15°	535.7	532.9	532.2	534.6	533.4	531.4	530.2	529.6	533.6	527.4	529.2
15.5°	537.9	526.4	531.4	528.3	530.6	528.8	526.8	530.1	530.9	525.7	524.2
16°	532.7	530.0	528.4	530.1	529.4	527.2	526.5	524.3	530.0	525.3	523.9
16.5°	530.9	526.0	528.0	525.4	527.3	526.2	524.6	523.1	528.4	526.6	520.1
17°	529.1	520.8	524.8	522.6	526.1	523.4	520.8	518.2	525.7	524.1	519.6
17.5°	526.3	519.0	522.4	520.7	524.2	522.8	521.4	517.4	525.4	517.9	519.2
18°	525.1	517.6	521.2	520.8	521.0	520.4	519.2	515.4	523.0	514.0	517.0
18.5°	521.6	515.1	520.1	516.5	520.3	519.9	516.4	511.2	520.6	512.4	514.6
19°	521.6	516.4	516.5	516.4	522.2	515.7	516.4	510.5	518.5	511.3	512.6
19.5°	520.9	514.9	512.6	514.2	517.9	514.4	511.4	509.8	513.4	507.8	508.7
20°	517.8	512.9	511.7	513.2	515.2	510.9	510.6	508.2	514.3	506.0	507.6
20.5°	514.9	511.0	509.6	509.2	513.8	510.8	509.4	506.4	510.7	504.5	506.9
21°	512.3	506.8	507.2	507.2	511.5	508.0	506.5	503.7	509.9	504.4	505.8
21.5°	509.0	503.0	505.7	507.0	508.0	504.3	506.0	501.1	506.9	500.8	504.3
22°	508.4	501.2	502.3	501.2	508.2	505.1	503.6	500.2	504.8	499.7	499.8



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	503.2	500.3	503.3	498.7	503.4	499.8	497.7	497.8	502.4	496.0	495.9
23°	503.9	498.1	497.9	496.0	502.8	497.1	497.4	495.2	499.4	494.7	495.1
23.5°	502.3	496.0	497.5	494.8	500.2	494.9	493.2	493.4	499.7	492.0	492.7
24°	498.7	494.0	496.9	492.9	495.0	491.1	492.7	490.3	495.8	489.1	489.6
24.5°	495.0	490.9	489.2	491.0	493.9	491.2	489.7	487.0	492.4	486.0	486.6
25°	491.9	488.1	488.2	489.7	491.9	488.4	486.6	482.2	491.0	484.0	483.9
25.5°	490.3	484.0	486.5	486.8	488.4	487.6	483.5	480.6	486.9	481.7	481.9
26°	486.7	484.4	484.4	483.4	486.4	485.2	481.0	479.7	483.6	478.6	478.6
26.5°	483.8	482.8	480.7	480.1	482.5	482.6	478.5	476.4	482.2	476.7	476.7
27°	481.4	479.4	477.4	477.4	480.7	480.4	475.7	472.5	476.5	473.2	474.6
27.5°	478.9	477.0	473.9	475.6	478.1	477.3	473.3	468.8	475.7	471.7	470.4
28°	477.3	474.0	471.8	473.9	475.1	472.8	470.9	467.0	472.5	467.8	466.8
28.5°	473.3	470.0	469.2	470.5	472.4	469.9	467.7	464.7	469.0	465.1	464.3
29°	470.8	466.0	469.2	466.6	471.1	466.5	464.4	460.7	465.7	462.4	461.1
29.5°	467.8	464.7	465.2	463.4	467.4	464.7	461.5	458.1	463.7	458.2	458.0
30°	463.7	461.4	462.7	461.8	463.1	460.0	458.9	456.0	459.7	456.4	456.2
30.5°	459.2	457.3	459.4	457.8	460.0	457.4	456.2	453.0	458.5	452.6	452.2
31°	457.8	455.2	455.7	453.7	457.5	454.8	452.9	450.3	456.3	449.3	448.0
31.5°	454.0	451.4	452.4	450.6	451.3	451.4	450.0	447.2	450.5	446.5	443.6
32°	449.7	447.2	448.6	448.5	449.1	448.7	446.8	443.9	446.7	443.3	440.1
32.5°	447.9	444.0	446.3	444.8	448.3	445.1	442.9	440.2	444.2	440.1	438.0
33°	445.2	442.5	442.9	440.6	442.2	441.0	439.4	436.2	441.1	436.4	434.8
33.5°	441.0	438.1	439.1	437.9	439.5	438.6	436.3	433.5	437.6	432.9	431.1
34°	436.7	434.2	435.5	435.3	436.1	435.3	432.7	430.3	434.3	430.4	426.6
34.5°	432.9	431.7	433.1	431.4	432.8	432.0	428.9	426.9	429.9	426.1	424.5
35°	429.5	428.0	428.3	428.3	430.6	428.6	425.3	422.6	427.9	421.9	420.4
35.5°	425.1	425.1	423.2	424.2	426.6	425.3	421.5	419.1	422.9	418.2	418.0
36°	421.2	419.9	420.4	420.4	423.4	421.4	417.4	415.2	420.0	414.2	414.7
36.5°	417.4	415.6	417.1	416.5	419.3	417.9	414.6	411.5	417.2	410.6	410.8
37°	413.5	411.7	412.6	412.1	415.2	414.0	411.3	407.6	411.9	406.5	406.8
37.5°	408.9	407.2	409.2	408.1	411.0	409.2	407.6	403.2	408.3	402.3	403.5
38°	404.9	401.9	405.0	405.0	406.7	405.4	403.6	398.1	403.8	398.1	396.1
38.5°	400.3	396.9	399.6	401.0	402.2	400.9	399.3	394.6	400.4	394.1	392.4
39°	396.0	393.2	394.7	396.1	397.6	396.8	394.4	392.0	395.2	389.8	387.7
39.5°	391.7	389.1	391.3	391.6	393.3	392.4	390.1	387.3	390.6	385.3	383.8
40°	386.5	384.1	385.9	386.2	388.7	387.7	385.3	382.4	385.8	380.9	378.5
40.5°	381.0	378.6	380.2	381.5	384.0	383.5	380.8	378.2	381.1	376.8	374.4
41°	375.7	374.4	376.2	377.4	379.4	377.5	376.4	372.9	377.4	371.7	369.9
41.5°	370.9	370.0	371.9	372.7	374.9	373.3	371.4	367.4	372.8	366.4	365.2
42°	365.7	365.2	366.0	367.5	369.9	368.5	366.4	364.1	368.1	360.7	360.3
42.5°	360.7	359.7	361.2	361.4	365.1	364.0	361.9	358.9	362.9	355.8	355.4
43°	355.4	355.3	356.7	356.3	360.6	359.4	357.6	354.7	357.2	351.2	349.9
43.5°	350.2	349.6	351.0	351.3	356.1	354.6	352.1	350.0	352.2	346.3	344.9
44°	345.2	343.9	346.2	345.4	350.8	349.9	346.9	343.2	347.2	341.3	339.6
44.5°	339.3	338.8	341.7	340.7	345.7	344.9	342.1	338.0	341.9	336.3	334.5



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	333.8	333.2	336.8	335.9	340.4	339.8	337.5	333.0	336.6	331.2	329.4
45.5°	328.8	328.0	331.1	331.5	335.2	334.6	332.3	328.3	331.4	326.1	324.3
46°	323.6	322.8	324.8	325.8	329.8	329.5	327.1	323.9	326.2	320.9	318.8
46.5°	317.9	317.3	319.2	320.1	324.6	324.4	321.9	318.2	320.2	315.2	313.6
47°	312.3	311.6	313.5	315.0	319.3	319.0	316.5	313.2	314.9	310.0	308.2
47.5°	306.6	305.4	307.9	309.9	314.1	313.6	311.2	308.6	309.2	304.5	302.4
48°	301.1	300.4	302.2	304.4	308.6	308.1	306.0	302.5	303.7	299.4	296.8
48.5°	295.8	295.4	297.3	299.1	303.0	302.7	300.5	298.0	298.1	293.6	291.0
49°	290.5	289.8	291.8	294.0	297.3	297.0	294.9	291.7	292.9	287.9	285.4
49.5°	284.6	284.0	286.5	288.7	292.0	291.4	289.4	285.6	287.5	282.0	280.2
50°	279.3	278.4	281.6	283.2	286.4	286.0	283.8	280.0	281.8	276.6	274.9
50.5°	273.4	273.0	276.3	277.8	280.4	280.4	278.4	275.0	276.1	270.8	269.5
51°	267.9	268.2	270.6	272.3	274.6	274.7	272.8	269.4	270.5	265.2	264.3
51.5°	262.2	262.7	264.8	267.0	269.0	268.8	267.3	263.8	264.7	259.6	258.7
52°	256.4	257.2	259.4	260.9	263.1	263.0	261.4	258.3	258.6	254.1	252.7
52.5°	251.0	251.3	253.5	255.0	257.3	257.1	255.5	252.4	252.7	248.3	246.4
53°	245.3	245.0	247.6	249.4	251.7	251.0	249.6	246.4	246.5	242.7	240.4
53.5°	239.4	239.3	241.5	244.1	246.1	245.4	243.4	240.1	240.8	236.9	235.0
54°	233.6	233.1	235.7	238.1	240.4	239.7	237.5	234.2	234.9	231.1	229.4
54.5°	228.3	227.3	230.3	231.8	234.3	234.3	231.8	228.1	228.9	225.3	223.8
55°	222.9	221.9	224.8	226.2	228.4	228.2	225.9	222.4	223.2	219.8	217.6
55.5°	217.0	216.4	219.3	221.0	222.9	222.5	220.4	216.8	217.5	213.7	211.9
56°	211.1	211.2	213.5	215.2	216.8	216.5	214.5	211.2	211.6	208.0	206.1
56.5°	205.7	205.9	208.2	209.8	211.0	210.7	208.6	205.5	205.9	202.1	200.2
57°	199.7	200.1	201.9	203.8	205.0	204.7	202.5	199.8	200.0	196.2	193.9
57.5°	193.4	194.5	195.8	197.5	198.9	198.8	196.3	194.0	194.5	190.4	188.1
58°	187.4	188.6	189.9	191.4	192.9	192.7	190.4	188.3	188.4	184.5	182.2
58.5°	181.2	182.8	184.6	185.8	186.8	186.6	184.6	182.3	182.2	178.6	176.6
59°	174.8	177.0	178.8	179.8	180.6	180.3	178.8	176.6	175.9	172.8	170.6
59.5°	168.3	170.9	173.0	173.8	174.8	174.3	173.1	170.6	169.6	167.0	164.9
60°	161.6	164.6	167.0	167.7	169.0	168.4	167.3	164.7	162.9	161.4	159.2
60.5°	155.0	158.5	160.8	161.4	163.4	162.6	161.4	158.8	156.7	155.5	153.5
61°	148.3	152.2	155.2	155.8	157.4	156.8	155.6	153.3	150.4	149.7	147.8
61.5°	142.0	146.0	149.4	149.9	151.6	151.2	150.0	147.4	143.8	143.5	142.2
62°	135.2	139.4	143.9	144.2	145.7	145.2	144.2	141.3	137.1	137.4	136.7
62.5°	128.2	132.8	137.9	138.3	139.8	139.1	138.3	134.6	130.2	131.0	130.7
63°	121.1	126.4	131.8	132.2	133.8	133.4	132.3	128.2	123.7	124.8	124.9
63.5°	114.2	120.5	126.2	126.2	128.1	127.8	126.6	121.9	117.1	118.4	119.3
64°	107.5	114.2	120.5	120.7	122.1	122.1	120.8	116.0	110.4	111.9	114.0
64.5°	101.1	107.6	114.9	114.8	116.4	116.1	115.0	109.5	103.8	105.4	108.3
65°	94.3	101.5	109.2	109.1	110.8	110.3	109.3	103.5	97.2	99.5	102.6
65.5°	88.1	95.2	103.4	103.6	105.2	104.4	103.6	97.6	90.9	93.6	97.1
66°	81.6	89.4	97.6	98.0	99.6	98.8	98.0	91.7	84.4	87.8	91.5
66.5°	75.3	83.6	92.1	92.4	94.2	93.2	92.6	86.0	78.1	82.1	86.3
67°	68.9	77.7	86.9	87.3	88.8	88.1	87.3	80.4	72.0	76.2	81.1



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	63.0	71.8	81.7	81.8	83.7	82.9	82.0	74.8	65.7	70.6	75.8
68°	57.3	66.6	76.5	76.7	78.4	77.7	76.8	69.4	59.8	65.1	70.5
68.5°	51.6	61.4	71.5	71.5	73.2	72.5	71.6	63.9	54.0	60.0	65.7
69°	45.9	56.3	66.5	66.6	68.1	67.4	66.5	59.0	48.4	55.0	61.1
69.5°	40.7	51.2	61.5	61.6	63.2	62.4	61.6	54.2	43.2	50.2	56.4
70°	35.7	46.5	56.8	56.9	58.4	57.7	56.8	49.7	38.4	45.6	52.0
70.5°	31.3	42.0	52.3	52.2	53.8	53.3	52.6	45.5	34.1	41.4	47.6
71°	27.8	38.0	47.7	47.8	49.4	48.8	48.1	41.3	30.3	37.3	43.5
71.5°	25.0	34.3	43.5	43.6	45.1	44.5	44.0	37.5	27.1	33.8	39.4
72°	23.1	30.9	39.4	39.8	41.1	40.6	40.0	34.0	24.8	30.6	35.8
72.5°	22.0	27.9	35.6	36.1	37.1	36.8	36.5	31.1	23.2	27.8	32.5
73°	21.0	25.5	32.3	32.8	33.6	33.4	33.0	28.4	22.1	25.6	29.4
73.5°	19.9	23.3	29.0	29.5	30.4	30.3	30.1	25.9	21.2	23.4	26.6
74°	18.8	21.4	26.0	26.8	27.6	27.5	27.3	23.8	20.1	21.7	24.3
74.5°	17.7	19.7	23.4	24.4	24.9	25.0	24.8	21.9	19.1	20.3	22.2
75°	16.8	18.3	21.4	22.3	22.5	23.1	22.7	20.4	18.0	18.8	20.7
75.5°	15.7	16.9	19.7	20.8	20.9	21.3	21.2	18.9	16.9	17.6	19.4
76°	14.8	16.0	18.4	19.6	19.6	20.1	19.8	17.7	15.8	16.5	18.4
76.5°	13.8	15.1	17.5	18.7	18.6	19.0	18.7	16.6	14.9	15.5	17.4
77°	12.9	14.2	16.7	17.8	17.7	18.1	17.8	15.6	13.9	14.5	16.5
77.5°	12.0	13.2	15.8	17.0	16.8	17.2	16.8	14.7	13.0	13.6	15.6
78°	11.1	12.4	15.0	16.1	16.0	16.3	16.0	13.8	12.1	12.6	14.6
78.5°	10.2	11.5	14.0	15.3	15.1	15.4	15.1	12.9	11.2	11.8	13.8
79°	9.4	10.6	13.2	14.4	14.3	14.6	14.3	12.0	10.4	10.9	12.9
79.5°	8.7	9.8	12.4	13.5	13.4	13.7	13.4	11.1	9.5	10.0	12.0
80°	7.8	8.9	11.5	12.7	12.7	12.9	12.6	10.2	8.6	9.2	11.2
80.5°	7.0	8.2	10.7	12.0	11.8	12.1	11.8	9.4	7.9	8.3	10.4
81°	6.3	7.4	9.9	11.1	11.2	11.4	11.0	8.5	7.1	7.6	9.6
81.5°	5.4	6.7	9.1	10.3	10.4	10.6	10.1	8.0	6.2	6.7	8.8
82°	4.7	5.9	8.5	9.6	9.6	9.8	9.2	6.9	5.3	6.1	8.4
82.5°	4.0	5.2	7.8	8.9	9.0	9.2	8.5	6.2	4.5	5.2	7.4
83°	3.3	4.6	7.0	8.1	8.3	8.4	7.8	5.5	4.1	4.5	6.6
83.5°	2.6	4.0	6.4	7.5	7.5	7.8	7.1	4.8	3.0	4.0	6.2
84°	2.0	2.8	5.8	6.8	6.8	7.1	6.4	4.0	2.2	3.2	5.3
84.5°	1.2	2.8	5.2	6.1	6.1	6.2	6.0	3.5	1.8	2.7	4.9
85°	1.2	2.6	4.7	5.4	5.3	5.5	5.2	2.9	1.0	2.1	4.2
85.5°	1.2	2.3	3.7	4.7	4.6	4.9	4.6	2.4	0.8	2.0	3.8
86°	1.1	2.0	3.6	4.1	4.1	4.1	4.2	2.1	0.6	1.7	3.0
86.5°	0.9	1.7	3.0	3.3	3.3	3.5	3.5	1.9	0.3	1.2	2.5
87°	0.7	1.3	2.5	2.8	2.7	2.9	2.9	1.3	0.1	1.0	2.0
87.5°	0.3	1.0	1.9	2.4	2.0	2.2	2.2	1.0	0.0	0.8	1.4
88°	0.2	0.7	1.4	1.7	1.6	2.0	2.0	0.7	0.0	0.2	0.8
88.5°	0.0	0.3	0.9	1.0	0.9	1.0	1.1	0.2	0.0	0.0	0.2
89°	0.0	0.1	0.4	0.6	0.3	0.6	0.8	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.1	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.2	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.2	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
128.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
129°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
129.5°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
130°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
130.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0
131°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.0	0.1	0.0	0.0
131.5°	0.1	0.1	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.0	0.0
132°	0.1	0.1	0.0	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0
132.5°	0.1	0.1	0.0	0.1	0.0	0.1	0.0	0.1	0.1	0.0	0.0
133°	0.1	0.1	0.0	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.0
133.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
134°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.1	0.0
134.5°	0.1	0.1	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.1	0.0



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.0	0.0	0.1	0.2	0.1	0.0	0.2	0.1	0.0	0.0
135.5°	0.1	0.0	0.0	0.1	0.1	0.1	0.0	0.2	0.1	0.0	0.0
136°	0.1	0.0	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.0	0.0
136.5°	0.1	0.0	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.0	0.0
137°	0.1	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.0	0.1
137.5°	0.1	0.0	0.0	0.1	0.1	0.2	0.1	0.1	0.2	0.0	0.0
138°	0.1	0.0	0.0	0.1	0.1	0.1	0.0	0.1	0.2	0.0	0.1
138.5°	0.1	0.0	0.0	0.1	0.1	0.2	0.0	0.1	0.2	0.1	0.0
139°	0.1	0.0	0.0	0.1	0.0	0.1	0.0	0.2	0.2	0.1	0.0
139.5°	0.1	0.0	0.0	0.1	0.0	0.1	0.1	0.1	0.2	0.1	0.0
140°	0.1	0.0	0.0	0.1	0.0	0.3	0.1	0.1	0.2	0.1	0.1
140.5°	0.1	0.1	0.0	0.1	0.0	0.2	0.1	0.1	0.2	0.1	0.1
141°	0.1	0.1	0.0	0.1	0.0	0.2	0.1	0.1	0.2	0.1	0.0
141.5°	0.1	0.1	0.0	0.1	0.2	0.2	0.2	0.3	0.2	0.2	0.0
142°	0.1	0.1	0.0	0.1	0.2	0.2	0.2	0.3	0.2	0.1	0.0
142.5°	0.1	0.1	0.0	0.1	0.3	0.3	0.1	0.2	0.3	0.1	0.0
143°	0.1	0.1	0.0	0.1	0.3	0.3	0.1	0.2	0.3	0.1	0.0
143.5°	0.1	0.1	0.0	0.1	0.2	0.3	0.1	0.2	0.3	0.2	0.0
144°	0.1	0.1	0.0	0.1	0.2	0.3	0.1	0.2	0.3	0.2	0.1
144.5°	0.1	0.1	0.1	0.1	0.2	0.3	0.1	0.3	0.3	0.1	0.1
145°	0.1	0.1	0.1	0.1	0.2	0.3	0.1	0.3	0.3	0.1	0.0
145.5°	0.3	0.1	0.1	0.1	0.3	0.3	0.1	0.3	0.3	0.1	0.0
146°	0.3	0.1	0.1	0.1	0.3	0.3	0.1	0.3	0.4	0.1	0.0
146.5°	0.3	0.4	0.1	0.1	0.3	0.3	0.1	0.3	0.4	0.1	0.0
147°	0.5	0.5	0.1	0.3	0.3	0.3	0.1	0.3	0.4	0.1	0.1
147.5°	0.5	0.5	0.2	0.3	0.3	0.3	0.1	0.3	0.4	0.1	0.1
148°	0.4	0.5	0.1	0.3	0.3	0.3	0.1	0.3	0.4	0.1	0.0
148.5°	0.4	0.5	0.3	0.3	0.3	0.4	0.1	0.3	0.5	0.2	0.0
149°	0.5	0.5	0.2	0.4	0.4	0.4	0.1	0.3	0.5	0.2	0.0
149.5°	0.6	0.5	0.3	0.5	0.3	0.3	0.1	0.4	0.5	0.2	0.0
150°	0.6	0.5	0.3	0.5	0.3	0.3	0.1	0.4	0.5	0.2	0.0
150.5°	0.7	0.5	0.5	0.5	0.3	0.4	0.1	0.4	0.5	0.3	0.1
151°	0.7	0.5	0.5	0.5	0.4	0.4	0.2	0.5	0.5	0.3	0.2
151.5°	0.7	0.7	0.5	0.5	0.4	0.4	0.2	0.5	0.5	0.3	0.3
152°	0.7	0.7	0.5	0.6	0.4	0.5	0.3	0.5	0.5	0.4	0.4
152.5°	0.7	0.7	0.5	0.7	0.5	0.5	0.3	0.5	0.6	0.4	0.1
153°	0.7	0.7	0.5	0.7	0.4	0.5	0.2	0.5	0.6	0.3	0.1
153.5°	0.7	0.7	0.5	0.7	0.5	0.5	0.2	0.5	0.6	0.3	0.1
154°	0.9	0.7	0.6	0.7	0.5	0.5	0.4	0.6	0.7	0.3	0.3
154.5°	0.9	0.7	0.7	0.7	0.6	0.6	0.5	0.6	0.7	0.4	0.3
155°	0.8	0.9	0.7	0.7	0.5	0.6	0.5	0.6	0.6	0.4	0.3
155.5°	0.9	1.0	0.7	0.7	0.5	0.6	0.5	0.7	0.7	0.4	0.3
156°	0.9	1.0	0.7	0.7	0.7	0.7	0.5	0.6	0.7	0.5	0.3
156.5°	0.9	0.9	0.7	0.7	0.6	0.7	0.5	0.6	0.7	0.5	0.5
157°	0.9	0.9	0.8	0.7	0.7	0.7	0.5	0.7	0.8	0.5	0.5



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.9	0.9	0.8	0.7	0.7	0.7	0.5	0.7	0.7	0.5	0.6
158°	0.9	0.9	0.8	0.7	0.7	0.7	0.6	0.8	0.8	0.6	0.6
158.5°	0.9	0.9	0.9	0.7	0.8	0.7	0.6	0.8	0.9	0.6	0.6
159°	0.9	0.9	1.0	0.8	0.7	0.7	0.6	0.8	0.8	0.7	0.6
159.5°	0.9	0.9	1.0	0.8	0.7	0.8	0.7	0.8	0.9	0.8	0.6
160°	0.9	0.9	0.9	0.9	0.8	0.8	0.7	0.8	0.9	0.8	0.6
160.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.7	0.9	0.9	0.8	0.7
161°	0.9	0.9	0.9	0.9	0.9	0.9	0.7	0.9	1.0	0.9	0.7
161.5°	0.9	1.1	0.9	0.9	0.9	0.9	0.8	1.0	1.0	0.9	0.7
162°	0.9	1.1	1.0	0.9	0.9	0.9	0.8	1.0	1.0	1.0	0.9
162.5°	0.9	1.1	1.0	0.9	1.0	1.0	0.8	0.9	1.0	1.0	0.9
163°	0.9	1.1	1.0	0.9	0.9	1.0	0.9	1.0	1.0	1.0	0.9
163.5°	0.9	1.1	1.1	0.9	0.9	1.0	1.0	1.0	1.0	1.0	0.9
164°	0.9	1.1	1.1	0.9	0.9	1.0	1.0	1.0	1.1	1.1	0.9
164.5°	0.9	1.1	1.1	0.9	1.0	1.0	1.0	1.0	1.1	1.1	0.9
165°	0.9	1.1	1.1	0.9	1.0	1.0	1.0	1.0	1.1	1.1	0.9
165.5°	0.9	1.1	1.1	1.0	1.0	1.1	1.0	1.0	1.2	1.1	0.9
166°	1.0	1.1	1.1	1.0	1.0	1.1	1.0	1.1	1.2	1.1	0.9
166.5°	1.0	1.1	1.1	1.0	1.1	1.1	1.0	1.1	1.2	1.1	0.9
167°	1.1	1.1	1.1	1.0	1.1	1.1	1.0	1.2	1.2	1.1	0.9
167.5°	1.1	1.1	1.1	1.0	1.1	1.1	1.0	1.2	1.2	1.1	1.0
168°	1.2	1.1	1.1	1.0	1.2	1.2	1.0	1.1	1.3	1.1	1.0
168.5°	1.2	1.1	1.1	1.0	1.1	1.1	1.0	1.1	1.2	1.1	1.1
169°	1.1	1.1	1.1	1.1	1.1	1.3	1.0	1.2	1.2	1.1	1.1
169.5°	1.1	1.1	1.1	1.1	1.1	1.2	1.0	1.2	1.2	1.1	1.1
170°	1.1	1.1	1.1	1.0	1.1	1.2	1.0	1.2	1.2	1.1	1.1
170.5°	1.1	1.1	1.1	1.0	1.3	1.2	1.0	1.2	1.2	1.1	1.1
171°	1.1	1.1	1.1	1.0	1.3	1.2	1.0	1.2	1.2	1.1	1.2
171.5°	1.1	1.1	1.1	1.0	1.2	1.2	1.0	1.2	1.2	1.1	1.1
172°	1.1	1.1	1.1	1.0	1.2	1.2	1.0	1.2	1.2	1.1	1.1
172.5°	1.1	1.1	1.1	1.0	1.2	1.2	1.0	1.2	1.2	1.1	1.1
173°	1.3	1.1	1.1	1.1	1.2	1.2	1.0	1.2	1.2	1.1	1.0
173.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
174°	1.2	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
174.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
175°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
175.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
176°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.0
176.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1
177°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.2	1.2	1.1	1.1
177.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1
178°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1
178.5°	1.3	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1
179°	1.2	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1
179.5°	1.2	1.1	1.1	1.2	1.2	1.2	1.0	1.1	1.2	1.1	1.1



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	559.6	559.6	559.6	559.6	559.6	559.6
0.5°	550.0	555.8	556.7	551.4	552.1	558.3
1°	554.9	555.6	555.4	553.4	551.9	558.9
1.5°	557.0	556.8	554.2	551.2	554.8	556.7
2°	555.8	555.4	557.4	553.8	552.4	559.6
2.5°	552.5	555.1	552.6	551.7	550.6	560.6
3°	552.9	553.5	553.3	555.4	549.6	558.5
3.5°	552.6	554.1	552.4	551.9	550.2	557.0
4°	549.2	553.5	553.4	550.7	548.8	559.1
4.5°	550.8	553.6	550.7	552.8	550.5	557.9
5°	550.0	552.1	555.3	551.3	550.9	557.2
5.5°	548.8	551.4	547.4	553.4	549.1	556.5
6°	551.2	551.8	551.9	545.9	546.7	555.2
6.5°	549.2	552.2	549.7	547.8	544.6	555.5
7°	548.8	548.8	551.8	544.1	547.8	553.7
7.5°	548.6	551.6	549.0	539.9	547.2	554.0
8°	547.0	547.3	551.2	540.0	545.7	552.5
8.5°	547.3	549.6	547.9	542.2	544.2	552.7
9°	542.6	546.0	546.6	543.7	541.8	553.0
9.5°	541.7	543.2	545.7	544.4	540.7	548.7
10°	541.8	544.5	543.2	542.9	541.1	547.0
10.5°	539.5	541.4	541.6	541.5	543.2	545.8
11°	537.4	539.2	542.2	539.1	540.0	544.4
11.5°	538.0	539.5	541.4	535.2	535.0	543.9
12°	534.9	535.8	536.4	533.9	534.2	543.2
12.5°	534.2	534.0	540.4	535.8	534.6	540.8
13°	533.6	536.9	535.0	535.2	532.0	539.4
13.5°	534.1	537.1	535.8	532.3	531.8	539.0
14°	530.3	531.2	533.2	531.5	529.8	538.7
14.5°	527.9	529.3	530.9	529.7	530.0	533.9
15°	527.0	528.1	528.3	526.6	526.9	535.7
15.5°	525.6	525.8	526.9	525.2	522.0	537.9
16°	524.8	526.0	525.9	524.6	519.9	532.7
16.5°	521.7	524.9	522.5	522.1	522.7	530.9
17°	520.7	523.5	522.4	520.1	517.6	529.1
17.5°	518.4	520.9	519.9	518.3	517.9	526.3
18°	517.1	518.1	517.9	516.7	516.4	525.1
18.5°	513.9	515.9	516.7	515.4	515.0	521.6
19°	512.4	514.2	512.4	514.2	511.1	521.6
19.5°	511.2	511.0	512.6	510.2	509.8	520.9
20°	511.1	508.9	507.8	508.6	508.7	517.8
20.5°	506.7	505.6	507.4	505.5	505.2	514.9
21°	499.9	503.1	507.4	503.3	500.5	512.3
21.5°	499.1	500.3	501.1	500.2	501.5	509.0
22°	498.3	498.0	499.6	498.6	499.5	508.4



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	496.3	497.8	495.5	496.0	497.1	503.2
23°	492.6	496.3	495.6	493.4	494.9	503.9
23.5°	492.0	494.5	491.2	492.1	493.3	502.3
24°	487.4	492.5	487.2	489.6	490.2	498.7
24.5°	486.3	489.1	485.0	486.7	489.0	495.0
25°	483.4	486.1	483.5	484.3	485.6	491.9
25.5°	481.2	482.9	482.4	480.8	480.8	490.3
26°	479.2	478.8	479.9	478.0	478.2	486.7
26.5°	474.6	476.0	479.0	477.3	477.2	483.8
27°	471.9	473.1	474.9	474.3	473.2	481.4
27.5°	469.5	472.8	471.8	469.1	470.7	478.9
28°	466.8	470.6	467.3	467.0	467.2	477.3
28.5°	464.0	467.0	465.5	465.8	463.8	473.3
29°	460.6	462.4	462.6	462.7	460.7	470.8
29.5°	457.6	458.8	456.8	458.6	456.7	467.8
30°	454.9	455.4	457.0	455.8	454.0	463.7
30.5°	451.9	452.1	451.2	453.0	452.7	459.2
31°	447.6	448.6	448.8	450.0	450.9	457.8
31.5°	443.4	446.6	446.6	446.9	447.2	454.0
32°	441.2	443.6	442.1	443.8	444.0	449.7
32.5°	439.5	439.2	439.7	440.0	438.8	447.9
33°	436.0	435.5	436.9	436.4	436.9	445.2
33.5°	432.2	432.0	432.6	432.7	434.1	441.0
34°	428.2	429.8	429.1	429.8	432.2	436.7
34.5°	425.7	426.6	425.4	426.9	427.1	432.9
35°	421.8	422.6	421.5	422.6	423.2	429.5
35.5°	417.7	418.1	418.6	419.1	419.4	425.1
36°	412.9	413.7	414.3	415.1	412.5	421.2
36.5°	409.0	409.8	410.3	410.3	408.4	417.4
37°	404.2	404.6	405.9	405.6	405.5	413.5
37.5°	400.3	400.3	401.2	401.0	402.0	408.9
38°	396.2	395.7	397.0	396.8	397.4	404.9
38.5°	392.1	391.8	392.1	392.6	392.7	400.3
39°	387.8	387.5	387.1	387.4	388.8	396.0
39.5°	383.4	382.2	382.1	383.2	384.1	391.7
40°	378.8	377.4	378.3	378.0	378.5	386.5
40.5°	373.9	372.6	374.2	373.2	373.1	381.0
41°	369.0	367.9	369.0	367.8	368.5	375.7
41.5°	363.9	363.7	364.4	363.6	365.2	370.9
42°	358.6	359.2	358.9	358.4	359.6	365.7
42.5°	353.3	354.5	354.3	353.5	353.6	360.7
43°	348.0	348.9	349.0	348.1	348.8	355.4
43.5°	343.2	343.2	344.3	342.9	344.0	350.2
44°	338.3	337.1	339.6	338.3	337.3	345.2
44.5°	333.2	333.0	334.1	332.8	332.5	339.3



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	328.2	327.5	328.4	327.2	327.9	333.8
45.5°	323.2	322.6	323.3	321.6	322.4	328.8
46°	317.9	319.4	318.3	317.0	316.7	323.6
46.5°	312.7	313.5	313.1	312.1	312.2	317.9
47°	307.0	308.0	307.9	306.8	306.9	312.3
47.5°	301.5	302.3	302.0	301.2	301.8	306.6
48°	296.3	297.0	296.2	296.0	296.2	301.1
48.5°	291.0	291.8	291.1	291.2	291.3	295.8
49°	285.6	285.8	285.2	285.7	285.6	290.5
49.5°	279.8	280.1	279.6	279.8	280.3	284.6
50°	273.9	274.5	274.1	274.0	274.1	279.3
50.5°	268.2	268.4	268.9	268.5	268.1	273.4
51°	262.7	262.8	263.5	263.0	262.9	267.9
51.5°	257.5	257.1	258.0	257.1	257.4	262.2
52°	251.8	251.9	252.3	251.8	251.6	256.4
52.5°	245.8	246.5	246.5	245.8	245.3	251.0
53°	239.7	240.4	240.4	240.0	240.6	245.3
53.5°	233.8	234.8	234.7	234.6	234.8	239.4
54°	227.8	228.8	228.9	228.6	229.0	233.6
54.5°	222.1	223.0	223.1	223.0	223.4	228.3
55°	216.5	217.2	217.5	217.3	217.2	222.9
55.5°	210.3	211.7	211.6	211.5	211.4	217.0
56°	204.6	205.8	205.1	205.8	206.0	211.1
56.5°	198.5	199.4	199.1	199.9	200.6	205.7
57°	192.6	193.2	193.2	193.5	194.4	199.7
57.5°	186.8	186.8	187.6	187.8	188.1	193.4
58°	180.8	180.7	181.6	181.8	182.6	187.4
58.5°	175.1	175.0	175.7	175.8	176.9	181.2
59°	169.3	169.2	169.5	169.7	171.2	174.8
59.5°	163.4	163.1	163.1	163.4	165.2	168.3
60°	157.4	157.1	156.4	157.6	159.4	161.6
60.5°	151.7	151.0	150.6	151.8	153.2	155.0
61°	145.9	145.4	144.5	145.6	147.1	148.3
61.5°	140.3	139.0	138.6	139.7	140.8	142.0
62°	134.5	132.8	133.0	134.0	134.4	135.2
62.5°	128.6	127.0	127.1	128.1	127.9	128.2
63°	122.8	121.2	121.1	122.2	121.4	121.1
63.5°	117.0	115.6	115.5	116.2	115.3	114.2
64°	111.1	110.0	109.8	110.4	108.9	107.5
64.5°	105.8	103.7	104.0	104.7	102.8	101.1
65°	100.2	98.0	98.3	98.8	96.8	94.3
65.5°	94.8	92.4	92.4	93.2	90.8	88.1
66°	89.3	87.1	86.9	87.9	84.7	81.6
66.5°	84.1	81.6	81.6	82.6	79.1	75.3
67°	78.8	76.4	76.3	77.3	73.6	68.9



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	73.5	71.3	71.2	72.0	68.2	63.0
68°	68.5	66.1	66.0	67.2	63.2	57.3
68.5°	63.7	61.4	61.1	62.3	58.0	51.6
69°	59.0	56.4	56.4	57.4	53.1	45.9
69.5°	54.4	51.8	51.9	53.0	48.4	40.7
70°	50.0	47.4	47.6	48.3	44.0	35.7
70.5°	45.9	43.3	43.4	44.2	39.9	31.3
71°	41.8	39.3	39.4	40.1	36.2	27.8
71.5°	38.0	35.7	35.8	36.4	32.7	25.0
72°	34.5	32.4	32.3	32.8	29.5	23.1
72.5°	31.3	29.3	29.2	29.7	26.8	22.0
73°	28.5	26.6	26.5	26.6	24.2	21.0
73.5°	26.0	24.2	24.2	24.1	22.1	19.9
74°	23.8	22.3	22.3	22.0	20.4	18.8
74.5°	22.0	21.1	20.9	20.5	18.7	17.7
75°	20.7	19.9	19.7	19.2	17.4	16.8
75.5°	19.5	18.9	18.9	18.3	16.4	15.7
76°	18.6	18.0	17.9	17.4	15.3	14.8
76.5°	17.8	17.1	17.0	16.4	14.4	13.8
77°	16.8	16.3	16.2	15.5	13.5	12.9
77.5°	15.9	15.4	15.3	14.7	12.6	12.0
78°	15.1	14.5	14.5	13.8	11.8	11.1
78.5°	14.3	13.8	13.6	13.0	11.0	10.2
79°	13.4	13.0	12.8	12.1	10.1	9.4
79.5°	12.5	12.1	12.1	11.3	9.2	8.7
80°	11.7	11.3	11.1	10.5	8.6	7.8
80.5°	11.0	10.5	10.4	9.8	7.7	7.0
81°	10.3	9.7	9.7	8.9	6.9	6.3
81.5°	9.4	9.0	9.0	8.2	6.2	5.4
82°	8.6	8.1	8.1	7.5	5.6	4.7
82.5°	8.2	7.4	7.4	6.8	4.9	4.0
83°	7.2	6.8	6.7	6.2	4.4	3.3
83.5°	6.4	5.9	5.9	5.7	3.8	2.6
84°	5.8	5.2	5.2	5.0	3.2	2.0
84.5°	4.9	4.6	4.6	4.6	2.9	1.2
85°	4.3	3.8	3.8	3.9	1.9	1.2
85.5°	3.8	3.1	3.2	3.1	2.0	1.2
86°	3.0	2.6	2.3	2.6	1.8	1.1
86.5°	2.4	2.1	2.0	2.1	1.5	0.9
87°	2.0	1.5	1.5	1.6	1.2	0.7
87.5°	1.1	1.0	1.0	1.1	0.9	0.3
88°	0.7	0.5	0.5	0.6	0.6	0.2
88.5°	0.1	0.1	0.0	0.2	0.3	0.0
89°	0.0	0.0	0.0	0.0	0.0	0.0
89.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.1	0.0
120.5°	0.0	0.0	0.0	0.0	0.1	0.0
121°	0.0	0.1	0.0	0.0	0.1	0.0
121.5°	0.0	0.1	0.0	0.0	0.1	0.0
122°	0.0	0.1	0.1	0.0	0.1	0.0
122.5°	0.0	0.1	0.1	0.1	0.1	0.0
123°	0.0	0.1	0.1	0.1	0.1	0.1
123.5°	0.0	0.1	0.1	0.1	0.1	0.1
124°	0.0	0.1	0.1	0.1	0.1	0.1
124.5°	0.0	0.1	0.2	0.1	0.1	0.1
125°	0.0	0.1	0.1	0.1	0.2	0.1
125.5°	0.0	0.1	0.1	0.1	0.1	0.1
126°	0.0	0.1	0.1	0.2	0.1	0.1
126.5°	0.0	0.1	0.1	0.2	0.1	0.1
127°	0.0	0.1	0.1	0.2	0.1	0.1
127.5°	0.0	0.1	0.1	0.2	0.0	0.2
128°	0.0	0.1	0.1	0.2	0.0	0.2
128.5°	0.0	0.1	0.1	0.2	0.0	0.1
129°	0.0	0.1	0.1	0.2	0.0	0.1
129.5°	0.0	0.1	0.1	0.2	0.0	0.1
130°	0.0	0.1	0.1	0.2	0.0	0.1
130.5°	0.0	0.1	0.1	0.2	0.0	0.1
131°	0.0	0.1	0.1	0.2	0.0	0.1
131.5°	0.0	0.1	0.1	0.2	0.0	0.1
132°	0.0	0.1	0.1	0.2	0.0	0.1
132.5°	0.0	0.1	0.1	0.2	0.0	0.1
133°	0.0	0.1	0.1	0.2	0.0	0.1
133.5°	0.0	0.1	0.1	0.2	0.0	0.1
134°	0.0	0.1	0.1	0.2	0.0	0.1
134.5°	0.1	0.1	0.1	0.2	0.0	0.1



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.1	0.1	0.2	0.1	0.1
135.5°	0.0	0.1	0.1	0.2	0.1	0.1
136°	0.1	0.1	0.1	0.2	0.2	0.1
136.5°	0.1	0.1	0.1	0.2	0.2	0.1
137°	0.1	0.1	0.1	0.2	0.1	0.1
137.5°	0.1	0.1	0.1	0.2	0.1	0.1
138°	0.1	0.1	0.1	0.2	0.1	0.1
138.5°	0.1	0.1	0.1	0.2	0.1	0.1
139°	0.1	0.1	0.1	0.2	0.1	0.1
139.5°	0.1	0.1	0.1	0.2	0.1	0.1
140°	0.1	0.1	0.1	0.2	0.1	0.1
140.5°	0.1	0.1	0.1	0.2	0.1	0.1
141°	0.1	0.1	0.1	0.2	0.1	0.1
141.5°	0.1	0.1	0.1	0.2	0.1	0.1
142°	0.1	0.1	0.1	0.2	0.1	0.1
142.5°	0.1	0.1	0.1	0.2	0.1	0.1
143°	0.2	0.1	0.1	0.2	0.1	0.1
143.5°	0.2	0.1	0.1	0.2	0.1	0.1
144°	0.2	0.1	0.1	0.2	0.1	0.1
144.5°	0.3	0.1	0.1	0.2	0.1	0.1
145°	0.2	0.1	0.1	0.2	0.1	0.1
145.5°	0.2	0.1	0.1	0.2	0.1	0.3
146°	0.3	0.1	0.1	0.2	0.2	0.3
146.5°	0.3	0.1	0.2	0.2	0.2	0.3
147°	0.3	0.2	0.1	0.2	0.2	0.5
147.5°	0.3	0.1	0.1	0.2	0.2	0.5
148°	0.3	0.1	0.4	0.2	0.2	0.4
148.5°	0.3	0.3	0.3	0.2	0.2	0.4
149°	0.3	0.2	0.4	0.2	0.2	0.5
149.5°	0.3	0.3	0.4	0.2	0.3	0.6
150°	0.3	0.3	0.4	0.2	0.3	0.6
150.5°	0.3	0.3	0.5	0.2	0.3	0.7
151°	0.3	0.3	0.5	0.3	0.3	0.7
151.5°	0.3	0.4	0.5	0.3	0.4	0.7
152°	0.4	0.4	0.7	0.3	0.3	0.7
152.5°	0.4	0.5	0.7	0.3	0.4	0.7
153°	0.5	0.5	0.7	0.3	0.5	0.7
153.5°	0.4	0.5	0.7	0.4	0.5	0.7
154°	0.4	0.5	0.7	0.5	0.6	0.9
154.5°	0.4	0.5	0.7	0.6	0.7	0.9
155°	0.5	0.5	0.7	0.7	0.8	0.8
155.5°	0.5	0.6	0.7	0.7	0.8	0.9
156°	0.5	0.7	0.7	0.7	0.7	0.9
156.5°	0.5	0.6	0.7	0.7	0.9	0.9
157°	0.6	0.6	0.7	0.8	0.9	0.9



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.6	0.6	0.7	0.8	0.9	0.9
158°	0.7	0.7	0.8	0.9	1.0	0.9
158.5°	0.7	0.8	0.8	0.9	1.0	0.9
159°	0.7	0.8	0.7	0.9	1.0	0.9
159.5°	0.8	0.8	0.8	0.9	1.0	0.9
160°	0.7	0.9	0.8	1.0	1.0	0.9
160.5°	0.7	0.9	0.8	1.0	1.0	0.9
161°	0.9	0.9	0.8	0.9	1.1	0.9
161.5°	0.9	1.0	0.8	1.0	1.1	0.9
162°	0.9	1.1	0.8	1.0	1.0	0.9
162.5°	1.0	1.0	0.9	1.0	1.0	0.9
163°	0.9	1.1	0.9	1.1	1.0	0.9
163.5°	1.0	1.1	1.0	1.1	1.0	0.9
164°	1.0	1.1	0.9	1.1	1.0	0.9
164.5°	1.0	1.1	1.1	1.1	1.0	0.9
165°	1.0	1.1	1.0	1.1	1.0	0.9
165.5°	1.0	1.1	1.0	1.1	1.2	0.9
166°	1.0	1.1	1.0	1.2	1.2	1.0
166.5°	1.0	1.1	1.0	1.1	1.1	1.0
167°	1.0	1.1	1.0	1.1	1.1	1.1
167.5°	1.0	1.1	1.0	1.1	1.1	1.1
168°	1.0	1.1	1.0	1.1	1.1	1.2
168.5°	1.0	1.2	1.0	1.1	1.1	1.2
169°	1.0	1.2	1.1	1.1	1.1	1.1
169.5°	1.0	1.1	1.1	1.1	1.1	1.1
170°	1.0	1.1	1.1	1.1	1.1	1.1
170.5°	1.0	1.1	1.1	1.1	1.1	1.1
171°	1.0	1.1	1.1	1.1	1.1	1.1
171.5°	1.0	1.1	1.1	1.1	1.1	1.1
172°	1.0	1.1	1.1	1.1	1.1	1.1
172.5°	1.0	1.1	1.1	1.1	1.1	1.1
173°	1.0	1.1	1.1	1.1	1.1	1.3
173.5°	1.0	1.1	1.1	1.1	1.1	1.3
174°	1.0	1.1	1.1	1.1	1.1	1.2
174.5°	1.0	1.1	1.1	1.1	1.1	1.3
175°	1.0	1.1	1.1	1.1	1.1	1.3
175.5°	1.0	1.1	1.1	1.1	1.1	1.3
176°	1.0	1.1	1.1	1.2	1.1	1.3
176.5°	1.0	1.1	1.1	1.1	1.1	1.3
177°	1.0	1.1	1.1	1.1	1.1	1.3
177.5°	1.0	1.2	1.1	1.2	1.1	1.3
178°	1.0	1.2	1.1	1.2	1.1	1.3
178.5°	1.0	1.2	1.1	1.2	1.1	1.3
179°	1.0	1.2	1.1	1.2	1.1	1.2
179.5°	1.0	1.2	1.1	1.2	1.1	1.2



TEST NUMBER: A1913422B001

CATALOG NUMBER: N/A

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	1.2	1.2	1.2	1.2	1.2	1.2

(END OF REPORT)