

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P199334

Luminaire Tested: **LT460WH6930**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P199334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P28071)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: LT460WH6930
Description: 4" LT LED RECESSED DOWNLIGHT

Light Source: EATON LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 574.8 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.23
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P199334
CATALOG NUMBER: LT460WH6930

Luminous Intensity Polar Plot





TEST NUMBER: P199334
 CATALOG NUMBER: LT460WH6930

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	96		97	95	93		93	91	90	88
2	102	95	90	85	100	94	88	84	90	86	82		87	83	80		84	81	78	76
3	95	86	79	73	92	84	78	72	81	76	71		79	74	70		76	72	69	67
4	88	77	69	63	85	76	69	63	73	67	62		71	66	61		69	64	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	50	74	63	55	49	61	54	49		59	53	49		58	52	48	46
7	70	58	50	45	69	57	50	44	56	49	44		54	48	44		53	48	44	42
8	66	53	46	40	64	53	45	40	51	45	40		50	44	40		49	44	39	38
9	62	49	42	37	60	49	41	36	48	41	36		47	41	36		46	40	36	34
10	58	46	38	33	57	45	38	33	44	38	33		43	37	33		43	37	33	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35289
5°	35424
10°	35045
15°	34785
20°	33957
25°	32759
30°	31576
35°	30040
40°	27711
45°	24491
50°	20667
55°	16795
60°	13543
65°	10799
70°	8764
75°	7053
80°	5256
85°	4529



TEST NUMBER: P199334
 CATALOG NUMBER: LT460WH6930

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.1	4.7
10°-20°	76.5	13.3
20°-30°	110.9	19.3
30°-40°	124.2	21.6
40°-50°	107.7	18.7
50°-60°	71.1	12.4
60°-70°	37.7	6.6
70°-80°	16.1	2.8
80°-90°	3.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	214.4	37.3
0°-40°	338.6	58.9
0°-60°	517.4	90.0
0°-90°	574.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	574.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	286	
5°	286	27
15°	272	76
25°	241	111
35°	200	124
45°	140	108
55°	78	71
65°	37	38
75°	15	16
85°	3	4
90°	0	



TEST NUMBER: P199334
CATALOG NUMBER: LT460WH6930

CANDELA DISTRIBUTION (FULL):

	0°
0°	286.1
2.5°	285.1
5°	286.1
7.5°	284.0
10°	279.8
12.5°	275.5
15°	272.4
17.5°	266.0
20°	258.7
22.5°	249.2
25°	240.7
27.5°	232.3
30°	221.7
32.5°	211.1
35°	199.5
37.5°	186.9
40°	172.1
42.5°	156.2
45°	140.4
47.5°	123.5
50°	107.7
52.5°	92.9
55°	78.1
57.5°	66.5
60°	54.9
62.5°	45.4
65°	37.0
67.5°	30.6
70°	24.3
72.5°	19.0
75°	14.8
77.5°	11.6
80°	7.4
82.5°	5.3
85°	3.2
87.5°	1.1
90°	0.0

(END OF REPORT)