

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886868

Luminaire Tested: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886868
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K
Description: 4IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1149.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.47 / 0.47 / 0.51
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 17.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886868
CATALOG NUMBER: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P886868
 CATALOG NUMBER: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90																			
3	105	100	96	92	104	99	95	92	96	93	90	94	91	89	92	89	88	86																			
4	101	95	91	87	100	94	90	87	92	88	86	90	87	85	88	86	84	82																			
5	98	91	86	83	96	90	86	82	88	84	82	87	83	81	85	82	80	79																			
6	94	87	82	79	93	86	82	78	85	81	78	84	80	77	82	79	77	76																			
7	91	84	79	75	90	83	78	75	82	78	75	81	77	74	80	76	74	73																			
8	88	80	76	72	87	80	75	72	79	75	72	78	74	72	77	74	71	70																			
9	85	77	73	69	84	77	72	69	76	72	69	75	72	69	75	71	69	68																			
10	82	75	70	67	82	74	70	67	74	70	67	73	69	67	72	69	66	65																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439863
5°	412384
10°	316277
15°	211543
20°	136748
25°	85442
30°	35650
35°	10435
40°	4315
45°	3628
50°	3665
55°	3720
60°	3626
65°	3794
70°	3751
75°	3717
80°	3694
85°	3680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 87.5°
 Luminance: 4807 cd/sqm



TEST NUMBER: P886868

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	291.6	25.4
10°-20°	463.6	40.3
20°-30°	280.7	24.4
30°-40°	56.9	5.0
40°-50°	16.6	1.4
50°-60°	15.4	1.3
60°-70°	12.8	1.1
70°-80°	8.4	0.7
80°-90°	3.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1035.8	90.1
0°-40°	1092.8	95.1
0°-60°	1124.8	97.9
0°-90°	1149.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1149.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3566	
5°	3331	292
15°	1657	464
25°	628	281
35°	69	57
45°	21	17
55°	17	15
65°	13	13
75°	8	8
85°	3	3
90°	0	



TEST NUMBER: P886868
CATALOG NUMBER: ML412LSFL95FS1E-TIR4D25NFL-TL4RDMW-1020LM-4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3566.1
2.5°	3531.5
5°	3330.6
7.5°	2976.4
10°	2525.2
12.5°	2074.9
15°	1656.6
17.5°	1329.3
20°	1041.8
22.5°	820.1
25°	627.8
27.5°	424.3
30°	250.3
32.5°	136.0
35°	69.3
37.5°	35.5
40°	26.8
42.5°	23.4
45°	20.8
47.5°	19.1
50°	19.1
52.5°	18.2
55°	17.3
57.5°	16.5
60°	14.7
62.5°	13.9
65°	13.0
67.5°	12.1
70°	10.4
72.5°	9.5
75°	7.8
77.5°	6.9
80°	5.2
82.5°	4.3
85°	2.6
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)