

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886932

Luminaire Tested: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K

Issue Date: 7/9/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886932  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-43)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 7/9/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K  
Description: 4IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, METALLIC SILVER TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1170.8 lumens  
Efficiency: N/A  
Efficacy: 66.5 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.77  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 17.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886932  
CATALOG NUMBER: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P886932

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																												
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90																												
3	105	99	94	91	103	98	94	90	95	92	89	93	90	87	90	88	86	85																												
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	81	80																												
5	96	88	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76																												
6	92	84	79	75	90	83	78	75	82	77	74	80	77	74	79	76	73	72																												
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																												
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65																												
9	81	72	67	64	80	72	67	64	71	66	63	70	66	63	69	66	63	62																												
10	78	69	64	61	77	69	64	60	68	63	60	67	63	60	67	63	60	59																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	238205
5°	227848
10°	209065
15°	189821
20°	167647
25°	137036
30°	82095
35°	24243
40°	5233
45°	1308
50°	959
55°	710
60°	617
65°	496
70°	289
75°	381
80°	568
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1308 cd/sqm



TEST NUMBER: P886932

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.3	14.5
10°-20°	414.4	35.4
20°-30°	444.4	38.0
30°-40°	127.7	10.9
40°-50°	8.1	0.7
50°-60°	3.2	0.3
60°-70°	1.9	0.2
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1029.0	87.9
0°-40°	1156.7	98.8
0°-60°	1168.0	99.8
0°-90°	1170.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1170.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1931	
5°	1840	170
15°	1486	414
25°	1007	444
35°	161	128
45°	8	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P886932

CATALOG NUMBER: ML412LSFL95FS1E-TIR4D55WFL-TL4RDSL-1020LM-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1931.2
2.5°	1918.7
5°	1840.2
7.5°	1755.1
10°	1669.2
12.5°	1578.3
15°	1486.5
17.5°	1388.1
20°	1277.2
22.5°	1150.4
25°	1006.9
27.5°	835.0
30°	576.4
32.5°	307.0
35°	161.0
37.5°	80.1
40°	32.5
42.5°	10.8
45°	7.5
47.5°	5.8
50°	5.0
52.5°	4.2
55°	3.3
57.5°	3.3
60°	2.5
62.5°	2.5
65°	1.7
67.5°	1.7
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)