

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640627

Luminaire Tested: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640627  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-30)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K  
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1261.3 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640627

CATALOG NUMBER: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640627

CATALOG NUMBER: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	93	85	80	76	92	85	79	75	83	78	75	81	77	74	80	76	73	72																			
6	89	81	75	71	88	80	74	70	78	74	70	77	73	69	76	72	69	68																			
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60																			
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57																			
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	165097
5°	160038
10°	139404
15°	114710
20°	89350
25°	68018
30°	49396
35°	33739
40°	21156
45°	12526
50°	4679
55°	2780
60°	1595
65°	635
70°	254
75°	336
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12526 cd/sqm



TEST NUMBER: P640627

CATALOG NUMBER: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	183.4	14.5
10°-20°	387.3	30.7
20°-30°	358.1	28.4
30°-40°	221.6	17.6
40°-50°	86.5	6.9
50°-60°	19.3	1.5
60°-70°	4.4	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	928.9	73.6
0°-40°	1150.5	91.2
0°-60°	1256.2	99.6
0°-90°	1261.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1261.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2091	
5°	2020	183
15°	1404	387
25°	781	358
35°	350	222
45°	112	86
55°	20	19
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P640627

CATALOG NUMBER: ML5612LSFL4097FS1E - 593SNB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2091.4
2.5°	2079.0
5°	2019.6
7.5°	1895.0
10°	1739.1
12.5°	1571.9
15°	1403.6
17.5°	1227.4
20°	1063.6
22.5°	914.4
25°	780.9
27.5°	657.5
30°	541.9
32.5°	439.8
35°	350.1
37.5°	273.8
40°	205.3
42.5°	156.0
45°	112.2
47.5°	66.2
50°	38.1
52.5°	28.0
55°	20.2
57.5°	14.6
60°	10.1
62.5°	7.9
65°	3.4
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)