

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640653

Luminaire Tested: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640653  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-28)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K  
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1020.7 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640653  
CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P640653

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	82	79	83	80	78	76																			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	67	64	63																			
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60																			
9	77	68	62	58	76	67	62	58	66	62	58	66	61	58	65	61	58	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132439
5°	128175
10°	111861
15°	91941
20°	71641
25°	54630
30°	39560
35°	27022
40°	16849
45°	10036
50°	3967
55°	2601
60°	1847
65°	1177
70°	1039
75°	1098
80°	1227
85°	1630

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10036 cd/sqm



TEST NUMBER: P640653

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.1	14.4
10°-20°	310.6	30.4
20°-30°	287.1	28.1
30°-40°	177.4	17.4
40°-50°	68.8	6.7
50°-60°	17.7	1.7
60°-70°	6.9	0.7
70°-80°	3.6	0.3
80°-90°	1.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.8	73.0
0°-40°	922.2	90.3
0°-60°	1008.7	98.8
0°-90°	1020.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1020.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1678	
5°	1618	147
15°	1125	311
25°	627	287
35°	280	177
45°	90	69
55°	19	18
65°	6	7
75°	4	4
85°	2	2
90°	0	



TEST NUMBER: P640653

CATALOG NUMBER: ML5612LSFL4097FS1E - 593WB - 600LM - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1677.7
2.5°	1666.9
5°	1617.5
7.5°	1521.3
10°	1395.5
12.5°	1258.9
15°	1125.0
17.5°	985.8
20°	852.8
22.5°	733.3
25°	627.2
27.5°	525.7
30°	434.0
32.5°	351.3
35°	280.4
37.5°	220.2
40°	163.5
42.5°	124.9
45°	89.9
47.5°	50.3
50°	32.3
52.5°	24.3
55°	18.9
57.5°	14.4
60°	11.7
62.5°	9.0
65°	6.3
67.5°	4.5
70°	4.5
72.5°	3.6
75°	3.6
77.5°	2.7
80°	2.7
82.5°	1.8
85°	1.8
87.5°	0.9
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)