

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640674

Luminaire Tested: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-33)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1423.9 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640674

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P640674

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																												
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																												
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																												
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																												
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	79	75	72	71																												
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																												
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																												
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																												
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																												
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182211
5°	176528
10°	153624
15°	126135
20°	98725
25°	74716
30°	53671
35°	36437
40°	23506
45°	15228
50°	8830
55°	4941
60°	3331
65°	2316
70°	1708
75°	1525
80°	1137
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15228 cd/sqm



TEST NUMBER: P640674

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.3	14.2
10°-20°	426.7	30.0
20°-30°	392.8	27.6
30°-40°	240.2	16.9
40°-50°	107.3	7.5
50°-60°	35.6	2.5
60°-70°	13.3	0.9
70°-80°	4.9	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1021.9	71.8
0°-40°	1262.1	88.6
0°-60°	1405.0	98.7
0°-90°	1423.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1423.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2308	
5°	2228	202
15°	1543	427
25°	858	393
35°	378	240
45°	136	107
55°	36	36
65°	12	13
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P640674

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2308.2
2.5°	2294.6
5°	2227.7
7.5°	2091.3
10°	1916.5
12.5°	1729.3
15°	1543.4
17.5°	1354.9
20°	1175.2
22.5°	1006.6
25°	857.8
27.5°	716.5
30°	588.8
32.5°	474.8
35°	378.1
37.5°	296.3
40°	228.1
42.5°	176.0
45°	136.4
47.5°	100.4
50°	71.9
52.5°	50.8
55°	35.9
57.5°	27.3
60°	21.1
62.5°	17.4
65°	12.4
67.5°	9.9
70°	7.4
72.5°	6.2
75°	5.0
77.5°	2.5
80°	2.5
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)