

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640692

Luminaire Tested: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640692
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1560.9 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640692
CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640692

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	86	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199815
5°	193470
10°	168261
15°	138353
20°	108084
25°	81893
30°	58703
35°	39935
40°	25763
45°	16534
50°	9677
55°	5423
60°	3647
65°	2540
70°	2193
75°	1647
80°	1227
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16534 cd/sqm



TEST NUMBER: P640692

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.7	14.2
10°-20°	467.7	30.0
20°-30°	430.4	27.6
30°-40°	263.2	16.9
40°-50°	117.6	7.5
50°-60°	39.0	2.5
60°-70°	14.7	0.9
70°-80°	5.9	0.4
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1119.7	71.7
0°-40°	1382.9	88.6
0°-60°	1539.5	98.6
0°-90°	1560.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1560.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2531	
5°	2442	222
15°	1693	468
25°	940	430
35°	414	263
45°	148	118
55°	39	39
65°	14	15
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P640692

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2531.2
2.5°	2514.8
5°	2441.5
7.5°	2290.7
10°	2099.1
12.5°	1896.7
15°	1692.9
17.5°	1483.6
20°	1286.6
22.5°	1103.2
25°	940.2
27.5°	785.3
30°	644.0
32.5°	520.4
35°	414.4
37.5°	324.7
40°	250.0
42.5°	194.3
45°	148.1
47.5°	110.1
50°	78.8
52.5°	55.7
55°	39.4
57.5°	29.9
60°	23.1
62.5°	19.0
65°	13.6
67.5°	10.9
70°	9.5
72.5°	6.8
75°	5.4
77.5°	4.1
80°	2.7
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)