

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P887107

Luminaire Tested: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

Issue Date: 7/9/2024

Test Information

Test Method: LM-79-2019
Report Number: P887107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-39)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/9/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K
Description: 4IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
Light Source: (1) D2W LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 842.5 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.64
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P887107

CATALOG NUMBER: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P887107

CATALOG NUMBER: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	104	99	95	92	96	93	90	94	91	89	92	89	88	86	86	86	86
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82	82	82	82
5	97	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	78	78	78	78
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75	75	75	75
7	90	83	78	74	89	82	78	74	81	77	74	80	76	73	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	71	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	228226
5°	221781
10°	199759
15°	169786
20°	129161
25°	73138
30°	29525
35°	5918
40°	2142
45°	1535
50°	1478
55°	1548
60°	1628
65°	1605
70°	1587
75°	1573
80°	1563
85°	1557

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 87.5°
 Luminance: 1697 cd/sqm



TEST NUMBER: P887107

CATALOG NUMBER: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.7	19.6
10°-20°	364.2	43.2
20°-30°	249.8	29.7
30°-40°	39.7	4.7
40°-50°	7.2	0.9
50°-60°	6.6	0.8
60°-70°	5.5	0.6
70°-80°	3.5	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.8	92.4
0°-40°	818.5	97.2
0°-60°	832.3	98.8
0°-90°	842.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	842.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1850	
5°	1791	165
15°	1330	364
25°	537	250
35°	39	40
45°	9	7
55°	7	7
65°	6	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P887107

CATALOG NUMBER: ML412LSFLD2W1E-TIR4D40FL-TL4RDMW-600LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1850.3
2.5°	1844.8
5°	1791.2
7.5°	1707.7
10°	1594.9
12.5°	1467.8
15°	1329.6
17.5°	1175.3
20°	984.0
22.5°	758.5
25°	537.4
27.5°	359.3
30°	207.3
32.5°	95.6
35°	39.3
37.5°	21.6
40°	13.3
42.5°	10.0
45°	8.8
47.5°	8.3
50°	7.7
52.5°	7.7
55°	7.2
57.5°	7.2
60°	6.6
62.5°	6.1
65°	5.5
67.5°	5.0
70°	4.4
72.5°	3.9
75°	3.3
77.5°	2.8
80°	2.2
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)