

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P382126

Luminaire Tested: **RA4069S1EWHMDMR-5000K**

Test Date: 12/10/2019

Test Information

Test Method: LM-41-14
Report Number: P382126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1912-596-4)
Test Lab: INNOVATION CENTER (G2)
Test Date: 12/10/2019
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RA4069S1EWHMDMR-5000K
Description: HALO RA Direct Mount Downlight 4" 5000K
Light Source: (24) 90 CRI LEDS
BRIDGELUX2835
Ballast/Driver: ELECTRICAL DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 814.5 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.14
Luminous Opening: Circular (Dia: 0.23' x H: 0')
CIE Type: Direct

Input Watts (W): 8.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P382126
CATALOG NUMBER: RA4069S1EWHMDMR-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P382126

CATALOG NUMBER: RA4069S1EWHMDMR-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	100	108	104	101	98	100	97	95		96	94	92		93	91	89	87
2	102	95	89	84	99	93	88	83	90	85	81		86	83	79		83	80	78	76
3	94	85	78	72	92	83	77	72	81	75	70		78	73	69		75	71	68	66
4	87	77	69	63	85	75	68	62	73	67	62		71	65	61		69	64	60	58
5	81	69	61	55	79	68	61	55	66	60	55		64	59	54		63	58	54	52
6	75	63	55	49	74	62	55	49	61	54	49		59	53	48		58	52	48	46
7	70	58	50	44	69	57	50	44	56	49	44		54	48	44		53	48	43	42
8	66	53	46	40	64	53	45	40	51	45	40		50	44	40		49	44	39	38
9	62	49	42	37	60	49	42	37	48	41	36		47	41	36		46	40	36	34
10	58	46	39	34	57	45	38	34	44	38	33		44	38	33		43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	112814
5°	112694
10°	110950
15°	109175
20°	105585
25°	100174
30°	93534
35°	83945
40°	75218
45°	65766
50°	57081
55°	49774
60°	42954
65°	37296
70°	32580
75°	28333
80°	25097
85°	21858



TEST NUMBER: P382126

CATALOG NUMBER: RA4069S1EWHMDMR-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.7	5.0
10°-20°	113.5	13.9
20°-30°	159.7	19.6
30°-40°	165.4	20.3
40°-50°	138.0	16.9
50°-60°	98.1	12.0
60°-70°	60.5	7.4
70°-80°	30.1	3.7
80°-90°	8.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.9	38.5
0°-40°	479.3	58.8
0°-60°	715.4	87.8
0°-90°	814.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	814.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	432	
5°	430	41
15°	404	113
25°	348	160
35°	264	165
45°	178	138
55°	109	98
65°	60	60
75°	28	30
85°	7	9
90°	0	



TEST NUMBER: P382126

CATALOG NUMBER: RA4069S1EWHMDMR-5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	432.3
2.5°	430.2
5°	430.2
7.5°	427.1
10°	418.7
12.5°	411.4
15°	404.1
17.5°	393.8
20°	380.2
22.5°	364.6
25°	347.9
27.5°	330.2
30°	310.4
32.5°	288.5
35°	263.5
37.5°	242.7
40°	220.8
42.5°	198.9
45°	178.2
47.5°	159.3
50°	140.6
52.5°	124.0
55°	109.4
57.5°	94.8
60°	82.3
62.5°	70.8
65°	60.4
67.5°	51.0
70°	42.7
72.5°	34.4
75°	28.1
77.5°	21.9
80°	16.7
82.5°	12.5
85°	7.3
87.5°	3.2
90°	0.0

(END OF REPORT)