

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640704

Luminaire Tested: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640704  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-32)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K  
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1425.1 lumens  
Efficiency: N/A  
Efficacy: 107.2 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640704  
CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640704

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	86	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	182432
5°	176639
10°	153624
15°	126315
20°	98683
25°	74768
30°	53598
35°	36456
40°	23516
45°	15094
50°	8830
55°	4955
60°	3331
65°	2316
70°	2008
75°	1525
80°	1137
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 15094 cd/sqm



TEST NUMBER: P640704

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	202.4	14.2
10°-20°	427.0	30.0
20°-30°	392.9	27.6
30°-40°	240.3	16.9
40°-50°	107.4	7.5
50°-60°	35.6	2.5
60°-70°	13.5	0.9
70°-80°	5.4	0.4
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1022.3	71.7
0°-40°	1262.6	88.6
0°-60°	1405.6	98.6
0°-90°	1425.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1425.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2311	
5°	2229	202
15°	1546	427
25°	858	393
35°	378	240
45°	135	107
55°	36	36
65°	12	13
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P640704

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2311.0
2.5°	2296.1
5°	2229.1
7.5°	2091.4
10°	1916.5
12.5°	1731.7
15°	1545.6
17.5°	1354.6
20°	1174.7
22.5°	1007.3
25°	858.4
27.5°	717.0
30°	588.0
32.5°	475.1
35°	378.3
37.5°	296.5
40°	228.2
42.5°	177.4
45°	135.2
47.5°	100.5
50°	71.9
52.5°	50.9
55°	36.0
57.5°	27.3
60°	21.1
62.5°	17.4
65°	12.4
67.5°	9.9
70°	8.7
72.5°	6.2
75°	5.0
77.5°	3.7
80°	2.5
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)