

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640712

Luminaire Tested: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640712  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-35)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K  
Description: ML56 RR, 40D TIR OPTIC, 5" SHALLOW WHITE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1000.7 lumens  
Efficiency: N/A  
Efficacy: 97.2 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640712

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640712

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94																			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67																			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																			
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	127411
5°	123460
10°	107693
15°	88697
20°	69340
25°	52757
30°	38293
35°	26318
40°	17230
45°	11142
50°	6337
55°	2656
60°	1800
65°	990
70°	600
75°	549
80°	409
85°	815

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11142 cd/sqm



TEST NUMBER: P640712

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.6	14.2
10°-20°	299.7	29.9
20°-30°	277.4	27.7
30°-40°	173.3	17.3
40°-50°	78.3	7.8
50°-60°	21.8	2.2
60°-70°	6.0	0.6
70°-80°	1.9	0.2
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	718.8	71.8
0°-40°	892.1	89.1
0°-60°	992.2	99.1
0°-90°	1000.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1000.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1614	
5°	1558	142
15°	1085	300
25°	606	277
35°	273	173
45°	100	78
55°	19	22
65°	5	6
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P640712

CATALOG NUMBER: ML5612LSFL4097FS1E - 596WB - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1614.0
2.5°	1604.4
5°	1558.0
7.5°	1464.3
10°	1343.5
12.5°	1214.0
15°	1085.3
17.5°	951.4
20°	825.4
22.5°	709.8
25°	605.7
27.5°	506.8
30°	420.1
32.5°	341.4
35°	273.1
37.5°	215.3
40°	167.2
42.5°	129.5
45°	99.8
47.5°	71.8
50°	51.6
52.5°	34.1
55°	19.3
57.5°	14.0
60°	11.4
62.5°	8.8
65°	5.3
67.5°	3.5
70°	2.6
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)