

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P599642

Luminaire Tested: **RL4069WZRGBWWH 2700K**

Issue Date: 5/31/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599642
 Test Lab: ETA TESTING TECHNOLOGY CO., LTD.
 Issue Date: 5/31/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: RL4069WZRGBWWH 2700K
 Description: 4 INCH RL WIZ SELECTABLE CCT
 Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: 630.83 (1 lamp)
 Luminaire Lumens: 614.9 lumens
 Efficiency: 97.5%
 Efficacy: 85.4 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.3
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.2
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599642
CATALOG NUMBER: RL4069WZRGBWWH 2700K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - · - · 90°-270° - · - · 135°-315°

TEST NUMBER: P599642
 CATALOG NUMBER: RL4069WZRGBWWH 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	116	116	116	116	113	113	113	113	108	108	108	104	104	104	99	99	99	99	99	99	99	99	99	97		
1	108	104	100	97	105	101	98	95	97	95	92	93	91	89	90	88	87	87	87	87	87	87	87	85		
2	99	92	86	81	96	90	85	80	87	82	78	83	80	76	81	77	75	75	75	75	75	75	75	73		
3	91	82	74	69	89	80	73	68	77	72	67	75	70	66	72	68	65	65	65	65	65	65	65	63		
4	84	73	65	59	82	72	64	59	69	63	58	67	62	57	65	60	56	56	56	56	56	56	56	54		
5	77	66	57	51	75	65	57	51	63	56	51	61	55	50	59	54	50	50	50	50	50	50	50	48		
6	72	59	51	45	70	58	51	45	57	50	45	55	49	44	54	48	44	44	44	44	44	44	44	42		
7	67	54	46	40	65	53	46	40	52	45	40	50	44	40	49	44	39	39	39	39	39	39	39	37		
8	62	49	42	36	61	49	41	36	48	41	36	46	40	36	45	40	35	35	35	35	35	35	35	34		
9	58	46	38	33	57	45	38	33	44	37	32	43	37	32	42	36	32	32	32	32	32	32	32	30		
10	54	42	35	30	53	42	34	30	41	34	30	40	34	29	39	33	29	29	29	29	29	29	29	28		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	33275	33275	33275	33275
5°	33288	33136	33162	33301
10°	33226	32983	32996	33213
15°	33080	32768	32781	33120
20°	32825	32357	32343	32866
25°	32340	31757	31757	32382
30°	31694	30924	30909	31723
35°	30742	29851	29820	30773
40°	29588	28503	28471	29604
45°	28067	26821	26786	28103
50°	26177	24728	24728	26216
55°	23806	22183	22161	23828
60°	20866	18953	19003	20916
65°	17093	15038	15068	17182
70°	12547	10303	10376	12658
75°	8315	6953	6953	8218
80°	7030	5653	5725	7102
85°	5487	3177	3321	5631

TEST NUMBER: P599642
 CATALOG NUMBER: RL4069WZRGBWWH 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	25.0	4.1	4.0
10°-20°	71.2	11.6	11.3
20°-30°	106.2	17.3	16.8
30°-40°	123.2	20.0	19.5
40°-50°	118.7	19.3	18.8
50°-60°	93.6	15.2	14.8
60°-70°	54.0	8.8	8.6
70°-80°	18.8	3.1	3.0
80°-90°	4.1	0.7	0.6
90°-100°	0.1	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	202.4	32.9	32.1
0°-40°	325.6	52.9	51.6
0°-60°	537.9	87.5	85.3
0°-90°	614.7	100.0	97.5
90°-120°	0.2	0.0	0.0
90°-150°	0.2	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	614.9	100.0	97.5

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	264	264	264	264	264	
5°	264	262	262	264	264	25
15°	254	252	252	254	254	72
25°	233	229	229	233	233	107
35°	200	194	194	200	200	125
45°	158	151	150	158	158	121
55°	108	101	101	109	108	97
65°	57	50	51	58	57	57
75°	17	14	14	17	17	21
85°	4	2	2	4	4	4
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P599642
 CATALOG NUMBER: RL4069WZRGBWWH 2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4	264.4
5°	263.5	263.4	262.9	262.8	262.3	262.2	262.2	262.3	262.5	262.6	263.3
10°	260.0	259.5	259.0	258.7	258.1	257.6	257.7	258.0	258.2	258.6	259.3
15°	253.9	253.7	252.6	252.1	251.5	250.9	251.1	250.6	251.6	251.8	252.8
20°	245.1	244.3	243.2	242.5	241.6	240.7	240.9	240.7	241.5	242.0	243.4
25°	232.9	232.1	230.5	230.0	228.7	227.7	227.9	227.7	228.7	229.0	230.8
30°	218.1	216.9	215.3	214.3	212.8	211.5	211.7	211.2	212.7	213.2	215.3
35°	200.1	199.2	197.2	195.9	194.3	192.7	192.7	192.5	194.1	195.1	197.5
40°	180.1	179.1	176.7	175.3	173.5	171.5	171.4	171.3	173.3	174.5	177.2
45°	157.7	156.7	154.2	152.7	150.7	148.5	148.3	148.3	150.5	151.9	155.0
50°	133.7	132.7	130.2	128.3	126.3	124.0	123.9	123.9	126.3	127.8	130.9
55°	108.5	107.5	104.7	103.0	101.1	98.8	99.0	98.8	101.0	102.6	105.7
60°	82.9	81.7	78.7	76.9	75.3	73.3	73.5	73.4	75.5	76.9	80.1
65°	57.4	56.0	53.0	51.4	50.5	48.8	49.1	48.9	50.6	51.7	54.7
70°	34.1	32.5	30.0	28.6	28.0	27.1	27.3	27.1	28.2	29.2	31.4
75°	17.1	16.2	15.3	14.5	14.3	14.1	13.9	14.2	14.3	15.2	15.5
80°	9.7	9.2	8.5	8.1	7.8	7.4	7.5	7.4	7.9	8.3	9.0
85°	3.8	3.5	2.7	2.4	2.2	1.8	1.9	1.9	2.3	2.6	3.3
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
95°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.1
105°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
110°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599642
 CATALOG NUMBER: RL4069WZRGBWWH 2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	264.4	264.4	264.4	264.4	264.4	264.4
5°	263.4	263.6	263.6	263.7	263.6	263.5
10°	259.8	259.9	260.4	260.5	260.4	260.0
15°	253.5	254.2	254.6	254.5	254.4	253.9
20°	244.3	245.4	246.0	246.1	245.8	245.1
25°	231.8	233.2	234.3	234.2	234.3	232.9
30°	216.7	218.3	219.6	219.5	219.4	218.1
35°	198.8	200.3	201.9	201.8	201.7	200.1
40°	178.7	180.2	181.6	181.3	181.6	180.1
45°	156.4	157.9	159.3	159.1	159.2	157.7
50°	132.5	133.9	135.3	134.9	135.3	133.7
55°	107.3	108.6	110.4	110.0	110.2	108.5
60°	81.8	83.1	84.9	84.5	84.6	82.9
65°	56.4	57.7	59.6	59.4	59.4	57.4
70°	33.1	34.4	36.0	36.1	35.8	34.1
75°	16.9	16.9	17.8	17.8	17.8	17.1
80°	9.5	9.8	10.3	10.3	10.3	9.7
85°	3.7	3.9	4.3	4.3	4.2	3.8
90°	0.1	0.1	0.1	0.1	0.1	0.1
95°	0.1	0.1	0.1	0.1	0.1	0.1
100°	0.1	0.1	0.1	0.1	0.1	0.0
105°	0.1	0.1	0.1	0.0	0.0	0.0
110°	0.1	0.1	0.1	0.0	0.0	0.0
115°	0.1	0.1	0.0	0.0	0.0	0.0
120°	0.1	0.1	0.0	0.0	0.0	0.0
125°	0.0	0.1	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.1	0.0	0.0	0.0	0.0
145°	0.0	0.1	0.0	0.0	0.0	0.0
150°	0.0	0.1	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)