

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P599645

Luminaire Tested: **RL4069WZRGBWWH 4000K**

Issue Date: 5/31/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P599645
 Test Lab: ETA TESTING TECHNOLOGY CO., LTD.
 Issue Date: 5/31/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: RL4069WZRGBWWH 4000K
 Description: 4 INCH RL WIZ SELECTABLE CCT
 Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: 630.83 (1 lamp)
 Luminaire Lumens: 604.9 lumens
 Efficiency: 95.9%
 Efficacy: 82.9 lumens/watt
 Spacing Criteria (0/90/45): 1.21 / 1.21 / 1.3
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P599645
CATALOG NUMBER: RL4069WZRGBWWH 4000K

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - · - 135°-315°

TEST NUMBER: P599645
 CATALOG NUMBER: RL4069WZRGBWWH 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	111	111	111	111	107	107	107	102	102	102	98	98	98	98	98	98	96
1	106	102	98	95	103	100	96	94	96	93	91	92	90	88	89	87	85	85	85	85	83
2	97	90	84	80	95	88	83	79	85	81	77	82	78	75	79	76	73	73	73	73	72
3	89	80	73	68	87	79	72	67	76	70	66	73	69	65	71	67	64	64	64	64	62
4	82	72	64	58	80	70	63	58	68	62	57	66	61	56	64	59	55	55	55	55	53
5	76	65	57	51	74	63	56	50	61	55	50	60	54	49	58	53	49	49	49	49	47
6	70	58	50	45	69	58	50	44	56	49	44	54	48	44	53	47	43	43	43	43	41
7	65	53	45	40	64	52	45	39	51	44	39	50	44	39	48	43	39	39	39	39	37
8	61	49	41	36	60	48	41	35	47	40	35	46	40	35	45	39	35	35	35	35	33
9	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	32	32	32	30
10	54	41	34	29	52	41	34	29	40	34	29	39	33	29	38	33	29	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	32734	32734	32734	32734
5°	32745	32593	32631	32758
10°	32676	32446	32459	32676
15°	32533	32234	32247	32572
20°	32290	31834	31821	32330
25°	31813	31243	31230	31854
30°	31185	30415	30401	31214
35°	30251	29360	29329	30281
40°	29111	28027	27994	29111
45°	27622	26376	26359	27640
50°	25746	24336	24317	25785
55°	23411	21810	21788	23455
60°	20539	18651	18676	20564
65°	16825	14800	14800	16884
70°	12327	10119	10192	12437
75°	8169	6807	6856	8072
80°	6885	5580	5653	6958
85°	5343	3177	3177	5487

TEST NUMBER: P599645
 CATALOG NUMBER: RL4069WZRGBWWH 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	24.6	4.1	3.9
10°-20°	70.1	11.6	11.1
20°-30°	104.5	17.3	16.6
30°-40°	121.1	20.0	19.2
40°-50°	116.7	19.3	18.5
50°-60°	92.1	15.2	14.6
60°-70°	53.1	8.8	8.4
70°-80°	18.5	3.1	2.9
80°-90°	4.0	0.7	0.6
90°-100°	0.1	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	199.1	32.9	31.6
0°-40°	320.3	53.0	50.8
0°-60°	529.1	87.5	83.9
0°-90°	604.7	100.0	95.9
90°-120°	0.2	0.0	0.0
90°-150°	0.2	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	604.9	100.0	95.9

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	260	260	260	260	260	
5°	259	258	258	259	259	25
15°	250	247	248	250	250	70
25°	229	225	225	229	229	105
35°	197	191	191	197	197	123
45°	155	148	148	155	155	119
55°	107	99	99	107	107	95
65°	56	50	50	57	56	56
75°	17	14	14	17	17	20
85°	4	2	2	4	4	4
90°	0	0	0	0	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P599645
 CATALOG NUMBER: RL4069WZRGBWWH 4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	260.1	260.1	260.1	260.1	260.1	260.1	260.1	260.1	260.1	260.1	260.1
5°	259.2	259.1	258.6	258.5	258.0	257.9	258.0	258.0	258.3	258.3	259.0
10°	255.7	255.2	254.8	254.5	253.9	253.5	253.5	253.8	254.0	254.3	255.1
15°	249.7	249.5	248.5	248.0	247.4	246.8	247.0	246.6	247.5	247.7	248.7
20°	241.1	240.3	239.2	238.5	237.7	236.8	237.0	236.8	237.6	238.0	239.5
25°	229.1	228.3	226.8	226.3	225.0	224.0	224.2	224.0	224.9	225.3	227.0
30°	214.6	213.4	211.8	210.8	209.3	208.1	208.3	207.8	209.2	209.8	211.8
35°	196.9	195.9	194.0	192.8	191.1	189.5	189.6	189.3	190.9	191.9	194.3
40°	177.2	176.1	173.8	172.5	170.6	168.7	168.7	168.5	170.4	171.6	174.3
45°	155.2	154.2	151.7	150.2	148.2	146.1	145.9	145.9	148.1	149.4	152.4
50°	131.5	130.5	128.1	126.2	124.3	122.0	121.9	121.8	124.2	125.7	128.8
55°	106.7	105.7	103.0	101.3	99.4	97.2	97.4	97.2	99.3	100.9	103.9
60°	81.6	80.4	77.4	75.6	74.1	72.1	72.3	72.2	74.2	75.7	78.8
65°	56.5	55.1	52.1	50.6	49.7	48.0	48.3	48.1	49.7	50.9	53.8
70°	33.5	32.0	29.5	28.1	27.5	26.6	26.8	26.7	27.7	28.7	30.8
75°	16.8	15.9	15.0	14.3	14.0	13.9	13.6	14.0	14.1	14.9	15.3
80°	9.5	9.1	8.3	7.9	7.7	7.3	7.4	7.3	7.8	8.1	8.8
85°	3.7	3.4	2.7	2.3	2.2	1.8	1.8	1.8	2.2	2.6	3.2
90°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
95°	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.1	0.1	0.1
100°	0.0	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.0	0.0	0.1
105°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
110°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P599645
 CATALOG NUMBER: RL4069WZRGBWWH 4000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	260.1	260.1	260.1	260.1	260.1	260.1
5°	259.1	259.3	259.4	259.4	259.3	259.2
10°	255.6	255.7	256.1	256.3	256.1	255.7
15°	249.4	250.0	250.5	250.4	250.2	249.7
20°	240.3	241.4	242.0	242.1	241.8	241.1
25°	228.1	229.4	230.5	230.4	230.5	229.1
30°	213.2	214.8	216.0	215.9	215.8	214.6
35°	195.6	197.1	198.6	198.5	198.4	196.9
40°	175.8	177.2	178.7	178.3	178.6	177.2
45°	153.9	155.3	156.7	156.5	156.7	155.2
50°	130.4	131.7	133.1	132.7	133.1	131.5
55°	105.6	106.9	108.6	108.2	108.4	106.7
60°	80.5	81.7	83.5	83.1	83.2	81.6
65°	55.4	56.7	58.7	58.5	58.5	56.5
70°	32.6	33.8	35.4	35.5	35.2	33.5
75°	16.7	16.6	17.5	17.5	17.5	16.8
80°	9.3	9.6	10.1	10.2	10.1	9.5
85°	3.6	3.8	4.3	4.2	4.2	3.7
90°	0.1	0.1	0.1	0.1	0.1	0.1
95°	0.1	0.1	0.1	0.1	0.1	0.1
100°	0.1	0.1	0.1	0.1	0.1	0.0
105°	0.1	0.1	0.1	0.0	0.0	0.0
110°	0.1	0.1	0.1	0.0	0.0	0.0
115°	0.1	0.1	0.0	0.0	0.0	0.0
120°	0.1	0.1	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)