

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P#

Luminaire Tested: **RL4069S1EWH -5000K**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P#
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25992-R2)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL4069S1EWH -5000K
Description: Halo RL 4in Downlight - SeleCCTable 5000K
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 598.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.25
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P#
CATALOG NUMBER: RL4069S1EWH -5000K

Luminous Intensity Polar Plot





TEST NUMBER: P#

CATALOG NUMBER: RL4069S1EWH -5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	100	108	104	101	98	100	97	95		96	94	92		93	91	89	87
2	102	95	89	84	99	93	87	83	89	85	81		86	82	79		83	80	77	75
3	94	85	77	72	92	83	76	71	80	74	70		78	73	69		75	71	67	65
4	87	76	68	62	85	75	67	62	72	66	61		70	64	60		68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	54		64	58	53		62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48		58	52	47		56	51	47	45
7	69	57	49	43	68	56	48	43	55	48	43		53	47	42		52	46	42	40
8	65	52	44	39	63	51	44	39	50	43	38		49	43	38		48	42	38	36
9	61	48	40	35	59	47	40	35	46	40	35		45	39	35		44	39	35	33
10	57	45	37	32	56	44	37	32	43	36	32		42	36	32		41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35213
5°	35208
10°	34938
15°	34787
20°	33897
25°	33063
30°	31970
35°	30512
40°	28766
45°	26412
50°	23416
55°	20142
60°	16386
65°	12715
70°	9420
75°	7780
80°	7755
85°	7653



TEST NUMBER: P#

CATALOG NUMBER: RL4069S1EWH -5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	4.4
10°-20°	74.9	12.5
20°-30°	109.5	18.3
30°-40°	124.1	20.7
40°-50°	114.2	19.1
50°-60°	82.0	13.7
60°-70°	43.3	7.2
70°-80°	18.0	3.0
80°-90°	5.5	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	210.8	35.3
0°-40°	334.9	56.0
0°-60°	531.1	88.8
0°-90°	598.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	598.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	279	26
15°	267	75
25°	238	109
35°	199	124
45°	148	114
55°	92	82
65°	43	43
75°	16	18
85°	5	6
90°	0	



TEST NUMBER: P#

CATALOG NUMBER: RL4069S1EWH -5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	279.8
2.5°	278.7
5°	278.7
7.5°	277.7
10°	273.4
12.5°	270.2
15°	267.0
17.5°	260.6
20°	253.1
22.5°	245.6
25°	238.1
27.5°	229.6
30°	220.0
32.5°	209.3
35°	198.6
37.5°	187.9
40°	175.1
42.5°	162.3
45°	148.4
47.5°	134.6
50°	119.6
52.5°	105.7
55°	91.8
57.5°	78.0
60°	65.1
62.5°	53.4
65°	42.7
67.5°	34.2
70°	25.6
72.5°	20.3
75°	16.0
77.5°	13.9
80°	10.7
82.5°	7.5
85°	5.3
87.5°	2.1
90°	0.0

(END OF REPORT)