

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P303274

Luminaire Tested: **RL4099BLE40AWH-3500K**

Test Date: 04/24/19

Test Information

Test Method: LM-41-14
Report Number: P303274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-161-2)
Test Lab: INNOVATION CENTER(G1)
Test Date: 04/24/19
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL4099BLE40AWH-3500K
Description: 4" RD LENS, 900LM, 90 BLE, 120V, MW, 3500K
Light Source: (30) 90 CRI LEDS
Ballast/Driver: ELECTRICAL DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 984.3 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.19
Luminous Opening: Circular (Dia: 0.27' x H: 0')
CIE Type: Direct


Input Watts (W): 10.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303274

CATALOG NUMBER: RL4099BLE40AWH-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303274

CATALOG NUMBER: RL4099BLE40AWH-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	102	96	90	85	100	94	88	84	90	86	82		87	84	80		84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71		79	74	70		76	72	69	67
4	88	77	70	64	86	76	69	63	74	68	63		71	66	62		69	65	61	59
5	81	70	62	56	80	69	62	56	67	61	55		65	59	55		63	58	54	52
6	76	64	56	50	74	63	55	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95682
5°	95316
10°	94540
15°	93158
20°	91066
25°	88339
30°	83969
35°	77780
40°	69294
45°	59982
50°	50549
55°	41957
60°	34529
65°	28251
70°	22562
75°	19203
80°	16893
85°	14792



TEST NUMBER: P303274

CATALOG NUMBER: RL4099BLE40AWH-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	4.9
10°-20°	135.6	13.8
20°-30°	196.6	20.0
30°-40°	211.8	21.5
40°-50°	175.2	17.8
50°-60°	116.3	11.8
60°-70°	64.3	6.5
70°-80°	28.8	2.9
80°-90°	7.5	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.5	38.7
0°-40°	592.3	60.2
0°-60°	883.7	89.8
0°-90°	984.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	984.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	512	
5°	508	48
15°	482	136
25°	428	197
35°	341	212
45°	227	175
55°	129	116
65°	64	64
75°	27	29
85°	7	7
90°	0	



TEST NUMBER: P303274

CATALOG NUMBER: RL4099BLE40AWH-3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	512.1
2.5°	511.1
5°	508.2
7.5°	504.2
10°	498.3
12.5°	491.4
15°	481.6
17.5°	470.7
20°	458.0
22.5°	444.3
25°	428.5
27.5°	410.9
30°	389.2
32.5°	365.6
35°	341.0
37.5°	313.6
40°	284.1
42.5°	255.5
45°	227.0
47.5°	199.5
50°	173.9
52.5°	150.4
55°	128.8
57.5°	109.1
60°	92.4
62.5°	77.6
65°	63.9
67.5°	52.1
70°	41.3
72.5°	33.4
75°	26.6
77.5°	20.7
80°	15.7
82.5°	10.8
85°	6.9
87.5°	2.0
90°	0.0

(END OF REPORT)