

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640781

Luminaire Tested: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-41)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K
Description: ML56 RR, 40D TIR OPTIC, 6" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1487.2 lumens
Efficiency: N/A
Efficacy: 90.1 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640781
CATALOG NUMBER: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P640781

CATALOG NUMBER: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	93	85	80	76	92	84	79	75	83	78	75	81	77	74	79	76	73	72																			
6	89	80	75	70	88	80	74	70	78	73	70	77	73	69	75	72	69	67																			
7	85	76	70	66	84	75	70	66	74	69	66	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57																			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134414
5°	130200
10°	113542
15°	93122
20°	72754
25°	55298
30°	40139
35°	27318
40°	17583
45°	10753
50°	5407
55°	2150
60°	1305
65°	519
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10753 cd/sqm



TEST NUMBER: P640781

CATALOG NUMBER: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.2	14.5
10°-20°	453.7	30.5
20°-30°	419.1	28.2
30°-40°	259.4	17.4
40°-50°	111.4	7.5
50°-60°	24.1	1.6
60°-70°	4.3	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1088.0	73.2
0°-40°	1347.4	90.6
0°-60°	1482.8	99.7
0°-90°	1487.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1487.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2452	
5°	2366	215
15°	1641	454
25°	914	419
35°	408	259
45°	139	111
55°	22	24
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640781

CATALOG NUMBER: ML5612LSFL4097FS1E - 693BB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2451.9
2.5°	2438.7
5°	2366.0
7.5°	2226.0
10°	2039.7
12.5°	1840.2
15°	1640.8
17.5°	1439.9
20°	1247.1
22.5°	1071.4
25°	914.2
27.5°	767.5
30°	634.1
32.5°	513.9
35°	408.2
37.5°	319.7
40°	245.7
42.5°	190.2
45°	138.7
47.5°	101.7
50°	63.4
52.5°	33.0
55°	22.5
57.5°	15.9
60°	11.9
62.5°	7.9
65°	4.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)