

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P303273

Luminaire Tested: **RL4099BLE40AWH-4000K**

Test Date: 04/24/19

Test Information

Test Method: LM-41-14
Report Number: P303273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-161-2)
Test Lab: INNOVATION CENTER(G1)
Test Date: 04/24/19
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: RL4099BLE40AWH-4000K
Description: 4" RD LENS, 900LM, 90 BLE, 120V, MW, 4000K
Light Source: (30) 90 CRI LEDS
Ballast/Driver: ELECTRICAL DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 992.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.19
Luminous Opening: Circular (Dia: 0.27' x H: 0')
CIE Type: Direct


Input Watts (W): 10.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303273

CATALOG NUMBER: RL4099BLE40AWH-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303273

CATALOG NUMBER: RL4099BLE40AWH-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95		97	95	93		93	91	90	88
2	102	96	90	85	100	94	88	84	90	86	82		87	84	80		84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71		79	74	70		76	72	69	67
4	88	77	70	64	86	76	69	63	74	68	63		71	66	62		69	65	61	59
5	81	70	62	56	80	69	62	56	67	61	55		65	59	55		63	58	54	52
6	76	64	56	50	74	63	55	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96430
5°	96048
10°	95280
15°	93874
20°	91782
25°	89040
30°	84638
35°	78396
40°	69806
45°	60457
50°	50985
55°	42282
60°	34790
65°	28472
70°	22726
75°	19347
80°	17108
85°	15006



TEST NUMBER: P303273

CATALOG NUMBER: RL4099BLE40AWH-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.6	4.9
10°-20°	136.7	13.8
20°-30°	198.2	20.0
30°-40°	213.5	21.5
40°-50°	176.6	17.8
50°-60°	117.2	11.8
60°-70°	64.8	6.5
70°-80°	29.0	2.9
80°-90°	7.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.4	38.7
0°-40°	596.9	60.2
0°-60°	890.6	89.8
0°-90°	992.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	992.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	516	
5°	512	49
15°	485	137
25°	432	198
35°	344	213
45°	229	177
55°	130	117
65°	64	65
75°	27	29
85°	7	8
90°	0	



TEST NUMBER: P303273

CATALOG NUMBER: RL4099BLE40AWH-4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	516.1
2.5°	515.1
5°	512.1
7.5°	508.2
10°	502.2
12.5°	495.3
15°	485.3
17.5°	474.4
20°	461.6
22.5°	447.7
25°	431.9
27.5°	414.1
30°	392.3
32.5°	368.5
35°	343.7
37.5°	316.0
40°	286.2
42.5°	257.5
45°	228.8
47.5°	201.0
50°	175.4
52.5°	151.5
55°	129.8
57.5°	110.0
60°	93.1
62.5°	78.2
65°	64.4
67.5°	52.5
70°	41.6
72.5°	33.7
75°	26.8
77.5°	20.8
80°	15.9
82.5°	10.9
85°	7.0
87.5°	2.0
90°	0.0

(END OF REPORT)