

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640805

Luminaire Tested: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1100.6 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640805
CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P640805

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94																
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88																
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82			82																
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76			76																
5	93	85	80	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			72																
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67			67																
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63			63																
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			60																
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56			56																
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53			53																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	98841
5°	95757
10°	83399
15°	68604
20°	53525
25°	40744
30°	29650
35°	20338
40°	13160
45°	8102
50°	4375
55°	1663
60°	1064
65°	376
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8102 cd/sqm



TEST NUMBER: P640805

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.1	14.4
10°-20°	334.0	30.3
20°-30°	308.9	28.1
30°-40°	192.6	17.5
40°-50°	84.1	7.6
50°-60°	19.3	1.8
60°-70°	3.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	801.0	72.8
0°-40°	993.5	90.3
0°-60°	1097.0	99.7
0°-90°	1100.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1100.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1803	
5°	1740	158
15°	1209	334
25°	674	309
35°	304	193
45°	104	84
55°	17	19
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640805

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 600LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1803.0
2.5°	1790.5
5°	1740.1
7.5°	1635.6
10°	1498.2
12.5°	1354.0
15°	1208.8
17.5°	1060.7
20°	917.5
22.5°	787.8
25°	673.6
27.5°	567.1
30°	468.4
32.5°	380.4
35°	303.9
37.5°	238.1
40°	183.9
42.5°	142.3
45°	104.5
47.5°	77.4
50°	51.3
52.5°	26.1
55°	17.4
57.5°	13.5
60°	9.7
62.5°	5.8
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)