

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640810

Luminaire Tested: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640810
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-42)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K
Description: ML56 RR, 40D TIR OPTIC, 6" SATIN NICKLE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1412.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.7
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640810
CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P640810

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94				94															
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88															
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82				82															
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76															
5	93	85	80	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72				72															
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67															
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63				63															
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60				60															
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56				56															
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	126810
5°	122854
10°	106995
15°	88020
20°	68670
25°	52273
30°	38044
35°	26093
40°	16882
45°	10396
50°	5612
55°	2141
60°	1360
65°	480
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10396 cd/sqm



TEST NUMBER: P640810

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.8	14.4
10°-20°	428.5	30.3
20°-30°	396.3	28.1
30°-40°	247.1	17.5
40°-50°	107.9	7.6
50°-60°	24.8	1.8
60°-70°	4.5	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1027.6	72.8
0°-40°	1274.7	90.3
0°-60°	1407.5	99.7
0°-90°	1412.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1412.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2313	
5°	2232	203
15°	1551	428
25°	864	396
35°	390	247
45°	134	108
55°	22	25
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640810

CATALOG NUMBER: ML5612LSFL4097FS1E - 693SNB - 900LM - 5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2313.2
2.5°	2297.1
5°	2232.5
7.5°	2098.4
10°	1922.1
12.5°	1737.1
15°	1550.9
17.5°	1360.9
20°	1177.1
22.5°	1010.7
25°	864.2
27.5°	727.6
30°	601.0
32.5°	488.0
35°	389.9
37.5°	305.5
40°	235.9
42.5°	182.5
45°	134.1
47.5°	99.3
50°	65.8
52.5°	33.5
55°	22.4
57.5°	17.4
60°	12.4
62.5°	7.5
65°	3.7
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)