

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640305

Luminaire Tested: ML5609LSFL40D2W1E - 592W - 900LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5609LSFL40D2W1E - 592W - 900LM - 2700K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) D2W SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1141.7 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 11.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640305
CATALOG NUMBER: ML5609LSFL40D2W1E - 592W - 900LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P640305

CATALOG NUMBER: ML5609LSFL40D2W1E - 592W - 900LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60																			
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148906
5°	144221
10°	125272
15°	103179
20°	80160
25°	60806
30°	43945
35°	30106
40°	18941
45°	11097
50°	4446
55°	2904
60°	2068
65°	1308
70°	1154
75°	1220
80°	1364
85°	906

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11097 cd/sqm



TEST NUMBER: P640305

CATALOG NUMBER: ML5609LSFL40D2W1E - 592W - 900LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.3	14.5
10°-20°	348.3	30.5
20°-30°	320.0	28.0
30°-40°	197.6	17.3
40°-50°	77.2	6.8
50°-60°	20.0	1.7
60°-70°	7.9	0.7
70°-80°	4.0	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.6	73.0
0°-40°	1031.2	90.3
0°-60°	1128.4	98.8
0°-90°	1141.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1141.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1886	
5°	1820	165
15°	1262	348
25°	698	320
35°	312	198
45°	99	77
55°	21	20
65°	7	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P640305

CATALOG NUMBER: ML5609LSFL40D2W1E - 592W - 900LM - 2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1886.3
2.5°	1873.2
5°	1820.0
7.5°	1711.5
10°	1562.8
12.5°	1412.2
15°	1262.5
17.5°	1105.8
20°	954.2
22.5°	819.6
25°	698.1
27.5°	584.6
30°	482.1
32.5°	390.7
35°	312.4
37.5°	245.1
40°	183.8
42.5°	140.6
45°	99.4
47.5°	57.3
50°	36.2
52.5°	28.1
55°	21.1
57.5°	16.1
60°	13.1
62.5°	11.0
65°	7.0
67.5°	5.0
70°	5.0
72.5°	4.0
75°	4.0
77.5°	3.0
80°	3.0
82.5°	2.0
85°	1.0
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)