

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640326

Luminaire Tested: ML5609LSFL40D2W1E - 692H - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-38)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5609LSFL40D2W1E - 692H - 900LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 6" HAZE TRIM
Light Source: (1) D2W SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1230.9 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 11.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640326
CATALOG NUMBER: ML5609LSFL40D2W1E - 692H - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640326

CATALOG NUMBER: ML5609LSFL40D2W1E - 692H - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	98	98	97	96	94																			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																			
4	98	91	85	81	96	90	85	81	87	83	80	86	82	79	84	81	78	77																			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72																			
6	89	80	75	70	87	80	74	70	78	73	70	77	72	69	75	72	69	67																			
7	85	76	70	66	83	75	70	66	74	69	65	73	68	65	72	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60																			
9	77	68	62	59	76	68	62	58	67	62	58	66	61	58	65	61	58	57																			
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111537
5°	107985
10°	93992
15°	77163
20°	60071
25°	45589
30°	33030
35°	22587
40°	14584
45°	8947
50°	4503
55°	1854
60°	1184
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8947 cd/sqm



TEST NUMBER: P640326

CATALOG NUMBER: ML5609LSFL40D2W1E - 692H - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.2	14.5
10°-20°	375.5	30.5
20°-30°	345.7	28.1
30°-40°	214.1	17.4
40°-50°	92.6	7.5
50°-60°	20.8	1.7
60°-70°	4.0	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	899.4	73.1
0°-40°	1113.5	90.5
0°-60°	1226.9	99.7
0°-90°	1230.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1230.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2035	
5°	1962	178
15°	1360	375
25°	754	346
35°	338	214
45°	115	93
55°	19	21
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640326

CATALOG NUMBER: ML5609LSFL40D2W1E - 692H - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2034.6
2.5°	2020.5
5°	1962.3
7.5°	1842.6
10°	1688.5
12.5°	1525.7
15°	1359.6
17.5°	1189.3
20°	1029.7
22.5°	884.1
25°	753.7
27.5°	632.9
30°	521.8
32.5°	423.7
35°	337.5
37.5°	264.2
40°	203.8
42.5°	157.4
45°	115.4
47.5°	85.2
50°	52.8
52.5°	28.0
55°	19.4
57.5°	15.1
60°	10.8
62.5°	6.5
65°	3.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)