

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640905

Luminaire Tested: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640905
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 5" HAZE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1580.1 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640905
CATALOG NUMBER: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P640905
 CATALOG NUMBER: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94						94													
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89						89													
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83						83													
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79						79													
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74						74													
6	91	82	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70						70													
7	87	78	73	69	86	78	72	69	76	72	68	75	71	68	74	71	68	66						66													
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63						63													
9	80	71	66	62	79	71	65	62	70	65	62	69	65	62	68	64	61	60						60													
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	61	59	57						57													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	332752
5°	304941
10°	227106
15°	135436
20°	85906
25°	67852
30°	53461
35°	41882
40°	31152
45°	17460
50°	4433
55°	2271
60°	1658
65°	560
70°	346
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17460 cd/sqm



TEST NUMBER: P640905

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	334.3	21.2
10°-20°	473.8	30.0
20°-30°	358.2	22.7
30°-40°	272.6	17.3
40°-50°	119.8	7.6
50°-60°	16.8	1.1
60°-70°	4.0	0.3
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1166.3	73.8
0°-40°	1438.8	91.1
0°-60°	1575.5	99.7
0°-90°	1580.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1580.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4215	
5°	3848	334
15°	1657	474
25°	779	358
35°	435	273
45°	156	120
55°	16	17
65°	3	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P640905

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592H - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4215.2
2.5°	4132.5
5°	3848.2
7.5°	3389.6
10°	2833.2
12.5°	2218.1
15°	1657.2
17.5°	1260.2
20°	1022.6
22.5°	887.2
25°	779.0
27.5°	675.2
30°	586.5
32.5°	505.3
35°	434.6
37.5°	372.9
40°	302.3
42.5°	225.6
45°	156.4
47.5°	82.7
50°	36.1
52.5°	22.6
55°	16.5
57.5°	13.5
60°	10.5
62.5°	6.0
65°	3.0
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)