

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640925

Luminaire Tested: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640925  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-2)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K  
Description: ML56 RR, 25D TIR OPTIC, 5" SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1029.0 lumens  
Efficiency: N/A  
Efficacy: 99.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.48  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640925

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640925

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	212430
5°	194604
10°	146209
15°	91018
20°	59015
25°	44082
30°	33344
35°	26386
40°	20146
45°	11666
50°	3095
55°	1335
60°	916
65°	355
70°	231
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11666 cd/sqm



TEST NUMBER: P640925

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.9	20.8
10°-20°	316.8	30.8
20°-30°	233.9	22.7
30°-40°	171.5	16.7
40°-50°	79.8	7.8
50°-60°	10.5	1.0
60°-70°	2.5	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	764.6	74.3
0°-40°	936.1	91.0
0°-60°	1026.4	99.7
0°-90°	1029.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1029.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2691	
5°	2456	214
15°	1114	317
25°	506	234
35°	274	172
45°	104	80
55°	10	10
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640925

CATALOG NUMBER: ML5612LSNFL2597FS1E - 592SC - 600LM - 5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2691.0
2.5°	2638.7
5°	2455.8
7.5°	2170.4
10°	1824.0
12.5°	1451.4
15°	1113.7
17.5°	872.8
20°	702.5
22.5°	592.2
25°	506.1
27.5°	427.7
30°	365.8
32.5°	314.5
35°	273.8
37.5°	236.1
40°	195.5
42.5°	148.0
45°	104.5
47.5°	59.0
50°	25.2
52.5°	14.5
55°	9.7
57.5°	7.7
60°	5.8
62.5°	3.9
65°	1.9
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)