

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640952

Luminaire Tested: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 837.4 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640952

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640952

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	98	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	65	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	62	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	185369
5°	169016
10°	123404
15°	70096
20°	42718
25°	34536
30°	28002
35°	22521
40°	17312
45°	9969
50°	2370
55°	1087
60°	837
65°	336
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9969 cd/sqm



TEST NUMBER: P640952

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.5	22.0
10°-20°	246.5	29.4
20°-30°	182.3	21.8
30°-40°	146.3	17.5
40°-50°	67.6	8.1
50°-60°	8.3	1.0
60°-70°	1.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.2	73.2
0°-40°	759.5	90.7
0°-60°	835.4	99.8
0°-90°	837.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	837.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2348	
5°	2133	184
15°	858	247
25°	396	182
35°	234	146
45°	89	68
55°	8	8
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640952

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 600LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2348.2
2.5°	2298.3
5°	2132.9
7.5°	1870.4
10°	1539.5
12.5°	1175.4
15°	857.7
17.5°	635.4
20°	508.5
22.5°	443.7
25°	396.5
27.5°	350.1
30°	307.2
32.5°	268.7
35°	233.7
37.5°	202.2
40°	168.0
42.5°	125.2
45°	89.3
47.5°	49.0
50°	19.3
52.5°	11.4
55°	7.9
57.5°	6.1
60°	5.3
62.5°	2.6
65°	1.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)