

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640957

Luminaire Tested: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640957
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K
Description: ML56 RR, 25D TIR OPTIC, 5" BLACK BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1074.3 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640957
CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640957

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94																			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89																			
3	104	98	93	90	102	97	92	89	94	91	88	92	89	86	89	87	85	83																			
4	99	92	87	83	98	91	86	83	89	85	82	87	84	81	85	82	80	79																			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	81	78	76	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	66	82	74	69	65	73	68	65	72	68	65	71	67	65	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	62	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	237825
5°	216847
10°	158321
15°	89931
20°	54806
25°	44309
30°	35923
35°	28891
40°	22218
45°	12783
50°	3033
55°	1390
60°	1058
65°	411
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12783 cd/sqm



TEST NUMBER: P640957

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.6	22.0
10°-20°	316.3	29.4
20°-30°	233.9	21.8
30°-40°	187.7	17.5
40°-50°	86.7	8.1
50°-60°	10.7	1.0
60°-70°	2.5	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.8	73.2
0°-40°	974.5	90.7
0°-60°	1071.8	99.8
0°-90°	1074.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3013	
5°	2736	237
15°	1100	316
25°	509	234
35°	300	188
45°	114	87
55°	10	11
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640957

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593BB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3012.7
2.5°	2948.7
5°	2736.5
7.5°	2399.6
10°	1975.1
12.5°	1508.0
15°	1100.4
17.5°	815.2
20°	652.4
22.5°	569.3
25°	508.7
27.5°	449.2
30°	394.1
32.5°	344.7
35°	299.8
37.5°	259.4
40°	215.6
42.5°	160.6
45°	114.5
47.5°	62.9
50°	24.7
52.5°	14.6
55°	10.1
57.5°	7.9
60°	6.7
62.5°	3.4
65°	2.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)