

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640482

Luminaire Tested: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640482
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-115)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K
Description: ML56 RR, MILKY OPTIC, 6" SHALLOW WHITE BAFFLE TRIM
Light Source: (1) D2W SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1119.9 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.28
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 11.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640482
CATALOG NUMBER: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640482

CATALOG NUMBER: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	101	95	89	85	91	87	83	88	84	81	85	82	80	78																			
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68																			
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	60																			
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53																			
6	76	64	57	51	75	64	56	51	62	55	50	60	54	50	59	54	49	48																			
7	71	59	51	46	69	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	44	40	39																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30348
5°	30283
10°	30154
15°	29949
20°	29595
25°	29119
30°	28359
35°	27318
40°	25820
45°	23545
50°	19291
55°	13897
60°	9561
65°	6564
70°	4664
75°	3643
80°	3725
85°	4088

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23545 cd/sqm



TEST NUMBER: P640482

CATALOG NUMBER: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	4.7
10°-20°	148.7	13.3
20°-30°	221.3	19.8
30°-40°	254.2	22.7
40°-50°	230.8	20.6
50°-60°	133.2	11.9
60°-70°	52.8	4.7
70°-80°	19.9	1.8
80°-90°	6.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.3	37.7
0°-40°	676.6	60.4
0°-60°	1040.6	92.9
0°-90°	1119.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1119.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	550	52
15°	528	149
25°	481	221
35°	408	254
45°	304	231
55°	145	133
65°	51	53
75°	17	20
85°	6	7
90°	0	



TEST NUMBER: P640482

CATALOG NUMBER: ML5609LSVWFLD2W1E - 696WB - 900LM - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	553.6
2.5°	552.5
5°	550.3
7.5°	547.1
10°	541.7
12.5°	535.3
15°	527.7
17.5°	518.0
20°	507.3
22.5°	495.4
25°	481.4
27.5°	465.3
30°	448.0
32.5°	428.6
35°	408.2
37.5°	384.5
40°	360.8
42.5°	333.9
45°	303.7
47.5°	268.2
50°	226.2
52.5°	184.2
55°	145.4
57.5°	113.1
60°	87.2
62.5°	66.8
65°	50.6
67.5°	38.8
70°	29.1
72.5°	22.6
75°	17.2
77.5°	15.1
80°	11.8
82.5°	9.7
85°	6.5
87.5°	2.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)