

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640999

Luminaire Tested: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640999
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 5" WHITE BAFFLE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1009.2 lumens
Efficiency: N/A
Efficacy: 98.0 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640999
CATALOG NUMBER: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P640999

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93			93																
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86			86																
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81			81																
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75			75																
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71			71																
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67																
7	85	76	70	66	83	75	69	66	74	69	65	72	68	65	71	67	64	63			63																
8	81	72	66	62	80	71	66	62	70	65	62	69	65	61	68	64	61	60			60																
9	78	68	63	59	77	68	62	59	67	62	59	66	62	58	65	61	58	57			57																
10	74	65	60	56	74	65	60	56	64	59	56	63	59	56	63	58	56	54			54																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205886
5°	188122
10°	137793
15°	79061
20°	48758
25°	39684
30°	32624
35°	26569
40°	20929
45°	12850
50°	4753
55°	3592
60°	3363
65°	3063
70°	3116
75°	3233
80°	3091
85°	3532

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12850 cd/sqm



TEST NUMBER: P640999

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	205.2	20.3
10°-20°	277.9	27.5
20°-30°	209.7	20.8
30°-40°	172.7	17.1
40°-50°	87.9	8.7
50°-60°	24.6	2.4
60°-70°	16.7	1.7
70°-80°	10.8	1.1
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.9	68.7
0°-40°	865.6	85.8
0°-60°	978.1	96.9
0°-90°	1009.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1009.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2608	
5°	2374	205
15°	967	278
25°	456	210
35°	276	173
45°	115	88
55°	26	25
65°	16	17
75°	11	11
85°	4	4
90°	0	



TEST NUMBER: P640999

CATALOG NUMBER: ML5612LSNFL2597FS1E - 593WB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2608.1
2.5°	2554.9
5°	2374.0
7.5°	2077.0
10°	1719.0
12.5°	1321.4
15°	967.4
17.5°	720.7
20°	580.4
22.5°	508.8
25°	455.6
27.5°	404.4
30°	357.9
32.5°	314.4
35°	275.7
37.5°	240.9
40°	203.1
42.5°	156.7
45°	115.1
47.5°	70.6
50°	38.7
52.5°	30.0
55°	26.1
57.5°	24.2
60°	21.3
62.5°	19.3
65°	16.4
67.5°	14.5
70°	13.5
72.5°	11.6
75°	10.6
77.5°	8.7
80°	6.8
82.5°	4.8
85°	3.9
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)