

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641006

Luminaire Tested: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1443.6 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641006

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K

Luminous Intensity Polar Plot





TEST NUMBER: P641006

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73			73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			68
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64			64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			57
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			54
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	279735
5°	254218
10°	185271
15°	105026
20°	64576
25°	52226
30°	42742
35°	34365
40°	27226
45°	21379
50°	16702
55°	13089
60°	10420
65°	8387
70°	6093
75°	3233
80°	1818
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21379 cd/sqm



TEST NUMBER: P641006

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	277.3	19.2
10°-20°	370.4	25.7
20°-30°	276.6	19.2
30°-40°	223.7	15.5
40°-50°	149.4	10.3
50°-60°	86.6	6.0
60°-70°	45.3	3.1
70°-80°	13.0	0.9
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	924.3	64.0
0°-40°	1148.0	79.5
0°-60°	1384.0	95.9
0°-90°	1443.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1443.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3544	
5°	3208	277
15°	1285	370
25°	600	277
35°	357	224
45°	192	149
55°	95	87
65°	45	45
75°	11	13
85°	0	1
90°	0	



TEST NUMBER: P641006

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 1200LM - 2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3543.6
2.5°	3465.7
5°	3208.1
7.5°	2809.2
10°	2311.3
12.5°	1771.1
15°	1285.1
17.5°	952.3
20°	768.7
22.5°	673.6
25°	599.6
27.5°	532.3
30°	468.9
32.5°	409.4
35°	356.6
37.5°	307.7
40°	264.2
42.5°	225.8
45°	191.5
47.5°	161.1
50°	136.0
52.5°	113.6
55°	95.1
57.5°	79.2
60°	66.0
62.5°	55.5
65°	44.9
67.5°	37.0
70°	26.4
72.5°	17.2
75°	10.6
77.5°	6.6
80°	4.0
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)