

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641017

Luminaire Tested: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641017  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K  
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1226.5 lumens  
Efficiency: N/A  
Efficacy: 92.2 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641017  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641017

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92																
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85																
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78																
4	96	88	82	78	94	87	81	77	84	80	76	82	78	75	81	77	74	73			73																
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			68																
6	86	77	71	67	85	76	71	66	75	70	66	74	69	66	72	68	65	64			64																
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			60																
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			57																
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			54																
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	55	52	51			51																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	237683
5°	215999
10°	157424
15°	89236
20°	54865
25°	44378
30°	36315
35°	29200
40°	23124
45°	18164
50°	14197
55°	11120
60°	8857
65°	7135
70°	5170
75°	2745
80°	1546
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18164 cd/sqm



TEST NUMBER: P641017

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	235.7	19.2
10°-20°	314.7	25.7
20°-30°	235.0	19.2
30°-40°	190.1	15.5
40°-50°	126.9	10.3
50°-60°	73.6	6.0
60°-70°	38.5	3.1
70°-80°	11.1	0.9
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	785.3	64.0
0°-40°	975.4	79.5
0°-60°	1175.9	95.9
0°-90°	1226.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1226.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3011	
5°	2726	236
15°	1092	315
25°	510	235
35°	303	190
45°	163	127
55°	81	74
65°	38	38
75°	9	11
85°	0	1
90°	0	



TEST NUMBER: P641017

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3010.9
2.5°	2944.7
5°	2725.8
7.5°	2386.9
10°	1963.9
12.5°	1504.9
15°	1091.9
17.5°	809.1
20°	653.1
22.5°	572.3
25°	509.5
27.5°	452.2
30°	398.4
32.5°	347.9
35°	303.0
37.5°	261.5
40°	224.4
42.5°	191.9
45°	162.7
47.5°	136.9
50°	115.6
52.5°	96.5
55°	80.8
57.5°	67.3
60°	56.1
62.5°	47.1
65°	38.2
67.5°	31.4
70°	22.4
72.5°	14.6
75°	9.0
77.5°	5.6
80°	3.4
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)