

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641019

Luminaire Tested: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1355.7 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641019

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641019

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 92 | | | 92 | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 94 | 105 | 100 | 96 | 93 | 97 | 93 | 91 | 94 | 91 | 89 | 91 | 89 | 87 | 85 | | | 85 | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 89 | 85 | 99 | 93 | 88 | 84 | 90 | 86 | 83 | 88 | 84 | 81 | 85 | 83 | 80 | 78 | | | 78 | | | | | | | | | | | | | | | | |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 81 | 77 | 84 | 80 | 76 | 82 | 78 | 75 | 81 | 77 | 74 | 73 | | | 73 | | | | | | | | | | | | | | | | |
| 5 | 91 | 82 | 76 | 72 | 89 | 81 | 76 | 71 | 79 | 74 | 71 | 78 | 73 | 70 | 76 | 72 | 69 | 68 | | | 68 | | | | | | | | | | | | | | | | |
| 6 | 86 | 77 | 71 | 67 | 85 | 76 | 71 | 66 | 75 | 70 | 66 | 74 | 69 | 66 | 72 | 68 | 65 | 64 | | | 64 | | | | | | | | | | | | | | | | |
| 7 | 82 | 73 | 67 | 62 | 81 | 72 | 66 | 62 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 64 | 61 | 60 | | | 60 | | | | | | | | | | | | | | | | |
| 8 | 79 | 69 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 58 | 66 | 62 | 58 | 65 | 61 | 58 | 57 | | | 57 | | | | | | | | | | | | | | | | |
| 9 | 75 | 66 | 60 | 56 | 74 | 65 | 59 | 56 | 64 | 59 | 55 | 63 | 59 | 55 | 62 | 58 | 55 | 54 | | | 54 | | | | | | | | | | | | | | | | |
| 10 | 72 | 63 | 57 | 53 | 71 | 62 | 57 | 53 | 61 | 56 | 53 | 61 | 56 | 53 | 60 | 55 | 52 | 51 | | | 51 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 262700 |
| 5° | 238734 |
| 10° | 173992 |
| 15° | 98627 |
| 20° | 60645 |
| 25° | 49047 |
| 30° | 40135 |
| 35° | 32274 |
| 40° | 25567 |
| 45° | 20073 |
| 50° | 15695 |
| 55° | 12290 |
| 60° | 9789 |
| 65° | 7883 |
| 70° | 5724 |
| 75° | 3020 |
| 80° | 1682 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20073 cd/sqm



TEST NUMBER: P641019

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 260.5 | 19.2 |
| 10°-20° | 347.8 | 25.7 |
| 20°-30° | 259.7 | 19.2 |
| 30°-40° | 210.1 | 15.5 |
| 40°-50° | 140.3 | 10.3 |
| 50°-60° | 81.4 | 6.0 |
| 60°-70° | 42.6 | 3.1 |
| 70°-80° | 12.2 | 0.9 |
| 80°-90° | 1.2 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 868.0 | 64.0 |
| 0°-40° | 1078.1 | 79.5 |
| 0°-60° | 1299.7 | 95.9 |
| 0°-90° | 1355.7 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1355.7 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3328 | |
| 5° | 3013 | 260 |
| 15° | 1207 | 348 |
| 25° | 563 | 260 |
| 35° | 335 | 210 |
| 45° | 180 | 140 |
| 55° | 89 | 81 |
| 65° | 42 | 43 |
| 75° | 10 | 12 |
| 85° | 0 | 1 |
| 90° | 0 | |



TEST NUMBER: P641019

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594SNB - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3327.8 |
| 2.5° | 3254.6 |
| 5° | 3012.7 |
| 7.5° | 2638.2 |
| 10° | 2170.6 |
| 12.5° | 1663.3 |
| 15° | 1206.8 |
| 17.5° | 894.3 |
| 20° | 721.9 |
| 22.5° | 632.6 |
| 25° | 563.1 |
| 27.5° | 499.8 |
| 30° | 440.3 |
| 32.5° | 384.5 |
| 35° | 334.9 |
| 37.5° | 289.0 |
| 40° | 248.1 |
| 42.5° | 212.1 |
| 45° | 179.8 |
| 47.5° | 151.3 |
| 50° | 127.8 |
| 52.5° | 106.7 |
| 55° | 89.3 |
| 57.5° | 74.4 |
| 60° | 62.0 |
| 62.5° | 52.1 |
| 65° | 42.2 |
| 67.5° | 34.7 |
| 70° | 24.8 |
| 72.5° | 16.1 |
| 75° | 9.9 |
| 77.5° | 6.2 |
| 80° | 3.7 |
| 82.5° | 2.5 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)