

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640587

Luminaire Tested: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640587
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1544.6 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640587

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P640587

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	85	76	70	66	83	75	69	66	74	69	65	73	68	65	71	68	65	63																			
8	81	72	66	62	80	71	66	62	70	65	61	69	64	61	68	64	61	60																			
9	77	68	62	58	76	67	62	58	67	62	58	66	61	58	65	61	58	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201441
5°	195103
10°	169480
15°	139587
20°	108445
25°	82259
30°	59450
35°	40726
40°	25629
45°	15015
50°	6005
55°	3922
60°	2795
65°	1775
70°	1569
75°	1647
80°	1864
85°	1268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15015 cd/sqm



TEST NUMBER: P640587

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	223.7	14.5
10°-20°	471.2	30.5
20°-30°	432.9	28.0
30°-40°	267.3	17.3
40°-50°	104.5	6.8
50°-60°	27.0	1.7
60°-70°	10.7	0.7
70°-80°	5.4	0.3
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.7	73.0
0°-40°	1395.0	90.3
0°-60°	1526.5	98.8
0°-90°	1544.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1544.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2552	
5°	2462	224
15°	1708	471
25°	944	433
35°	423	267
45°	134	104
55°	28	27
65°	10	11
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P640587

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 1200LM - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2551.8
2.5°	2534.2
5°	2462.1
7.5°	2315.4
10°	2114.3
12.5°	1910.5
15°	1708.0
17.5°	1496.0
20°	1290.9
22.5°	1108.8
25°	944.4
27.5°	790.8
30°	652.2
32.5°	528.6
35°	422.6
37.5°	331.5
40°	248.7
42.5°	190.2
45°	134.5
47.5°	77.5
50°	48.9
52.5°	38.0
55°	28.5
57.5°	21.7
60°	17.7
62.5°	14.9
65°	9.5
67.5°	6.8
70°	6.8
72.5°	5.4
75°	5.4
77.5°	4.1
80°	4.1
82.5°	2.7
85°	1.4
87.5°	1.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)