

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641022

Luminaire Tested: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641022  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K  
Description: ML56 RR, 25D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1486.2 lumens  
Efficiency: N/A  
Efficacy: 90.1 lumens/watt  
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.43  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641022  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641022

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	78			78
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	81	77	74	73			73
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68			68
6	86	77	71	67	85	76	71	66	75	70	66	73	69	65	72	68	65	64			64
7	82	73	67	62	81	72	66	62	71	66	62	70	65	62	69	64	61	60			60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57			57
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54			54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	287321
5°	261405
10°	190730
15°	108213
20°	66517
25°	53707
30°	43826
35°	35339
40°	27988
45°	21982
50°	17181
55°	13460
60°	10720
65°	8873
70°	6278
75°	3325
80°	2455
85°	1268

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21982 cd/sqm



TEST NUMBER: P641022

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	284.8	19.2
10°-20°	381.6	25.7
20°-30°	284.4	19.1
30°-40°	230.1	15.5
40°-50°	153.9	10.4
50°-60°	89.1	6.0
60°-70°	46.9	3.2
70°-80°	13.6	0.9
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.7	64.0
0°-40°	1180.9	79.5
0°-60°	1423.8	95.8
0°-90°	1486.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1486.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3640	
5°	3299	285
15°	1324	382
25°	617	284
35°	367	230
45°	197	154
55°	98	89
65°	48	47
75°	11	14
85°	1	2
90°	0	



TEST NUMBER: P641022

CATALOG NUMBER: ML5612LSNFL2597FS1E - 594TBZB - 1200LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3639.7
2.5°	3559.6
5°	3298.8
7.5°	2879.1
10°	2379.4
12.5°	1823.9
15°	1324.1
17.5°	981.9
20°	791.8
22.5°	692.6
25°	616.6
27.5°	547.3
30°	480.8
32.5°	422.4
35°	366.7
37.5°	316.4
40°	271.6
42.5°	232.2
45°	196.9
47.5°	167.0
50°	139.9
52.5°	116.8
55°	97.8
57.5°	81.5
60°	67.9
62.5°	57.0
65°	47.5
67.5°	38.0
70°	27.2
72.5°	17.7
75°	10.9
77.5°	6.8
80°	5.4
82.5°	2.7
85°	1.4
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)