

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640593

Luminaire Tested: ML5612LSFL4097FS1E - 592W - 600LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-27)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 592W - 600LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1021.6 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640593
CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 600LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640593

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 600LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 100 | 98 | 97 | 96 | 95 | 94 | | | | | | | | | | | | | | | | | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 102 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 93 | 91 | 89 | 87 | | | | | | | | | | | | | | | | | | | |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | 90 | 87 | 84 | 88 | 85 | 83 | 81 | | | | | | | | | | | | | | | | | | | |
| 4 | 98 | 90 | 85 | 81 | 96 | 89 | 84 | 80 | 87 | 83 | 79 | 85 | 82 | 79 | 83 | 80 | 78 | 76 | | | | | | | | | | | | | | | | | | | |
| 5 | 93 | 85 | 79 | 75 | 92 | 84 | 79 | 75 | 82 | 78 | 74 | 81 | 77 | 73 | 79 | 76 | 73 | 71 | | | | | | | | | | | | | | | | | | | |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 69 | 75 | 71 | 68 | 67 | | | | | | | | | | | | | | | | | | | |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 66 | 74 | 69 | 65 | 73 | 68 | 65 | 71 | 68 | 65 | 63 | | | | | | | | | | | | | | | | | | | |
| 8 | 81 | 72 | 66 | 62 | 80 | 71 | 66 | 62 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 60 | | | | | | | | | | | | | | | | | | | |
| 9 | 77 | 68 | 62 | 58 | 76 | 67 | 62 | 58 | 67 | 62 | 58 | 66 | 61 | 58 | 65 | 61 | 58 | 56 | | | | | | | | | | | | | | | | | | | |
| 10 | 74 | 65 | 59 | 55 | 73 | 64 | 59 | 55 | 63 | 58 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 54 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 133236 |
| 5° | 129046 |
| 10° | 112094 |
| 15° | 92325 |
| 20° | 71725 |
| 25° | 54404 |
| 30° | 39323 |
| 35° | 26935 |
| 40° | 16952 |
| 45° | 9936 |
| 50° | 3979 |
| 55° | 2601 |
| 60° | 1847 |
| 65° | 1177 |
| 70° | 1039 |
| 75° | 1098 |
| 80° | 1227 |
| 85° | 815 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9936 cd/sqm



TEST NUMBER: P640593

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 600LM - 3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 147.9 | 14.5 |
| 10°-20° | 311.7 | 30.5 |
| 20°-30° | 286.3 | 28.0 |
| 30°-40° | 176.8 | 17.3 |
| 40°-50° | 69.1 | 6.8 |
| 50°-60° | 17.9 | 1.8 |
| 60°-70° | 7.1 | 0.7 |
| 70°-80° | 3.6 | 0.3 |
| 80°-90° | 1.3 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 745.9 | 73.0 |
| 0°-40° | 922.7 | 90.3 |
| 0°-60° | 1009.6 | 98.8 |
| 0°-90° | 1021.6 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1021.6 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1688 | |
| 5° | 1628 | 148 |
| 15° | 1130 | 312 |
| 25° | 625 | 286 |
| 35° | 280 | 177 |
| 45° | 89 | 69 |
| 55° | 19 | 18 |
| 65° | 6 | 7 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P640593

CATALOG NUMBER: ML5612LSFL4097FS1E - 592W - 600LM - 3500K

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 1687.8 |
| 2.5° | 1676.1 |
| 5° | 1628.5 |
| 7.5° | 1531.4 |
| 10° | 1398.4 |
| 12.5° | 1263.6 |
| 15° | 1129.7 |
| 17.5° | 989.5 |
| 20° | 853.8 |
| 22.5° | 733.3 |
| 25° | 624.6 |
| 27.5° | 523.0 |
| 30° | 431.4 |
| 32.5° | 349.6 |
| 35° | 279.5 |
| 37.5° | 219.3 |
| 40° | 164.5 |
| 42.5° | 125.8 |
| 45° | 89.0 |
| 47.5° | 51.2 |
| 50° | 32.4 |
| 52.5° | 25.2 |
| 55° | 18.9 |
| 57.5° | 14.4 |
| 60° | 11.7 |
| 62.5° | 9.9 |
| 65° | 6.3 |
| 67.5° | 4.5 |
| 70° | 4.5 |
| 72.5° | 3.6 |
| 75° | 3.6 |
| 77.5° | 2.7 |
| 80° | 2.7 |
| 82.5° | 1.8 |
| 85° | 0.9 |
| 87.5° | 0.9 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)