

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641070

Luminaire Tested: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K
Description: ML56 RR, 25D TIR OPTIC, 6" DEADFRONT TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1629.7 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641070

CATALOG NUMBER: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P641070

CATALOG NUMBER: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	91	94	92	90	92	90	88	86																			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80																			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74																			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69																			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65																			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58																			
9	76	67	61	57	75	66	61	57	65	60	57	64	60	56	63	59	56	55																			
10	73	63	58	54	72	63	58	54	62	57	54	61	57	54	61	57	53	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221073
5°	202327
10°	147398
15°	84728
20°	51869
25°	41972
30°	34417
35°	28041
40°	22571
45°	18048
50°	14217
55°	9185
60°	3618
65°	2724
70°	2164
75°	1906
80°	1894
85°	1887

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18048 cd/sqm



TEST NUMBER: P641070

CATALOG NUMBER: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	317.0	19.5
10°-20°	428.1	26.3
20°-30°	319.8	19.6
30°-40°	262.8	16.1
40°-50°	181.2	11.1
50°-60°	86.9	5.3
60°-70°	20.9	1.3
70°-80°	9.7	0.6
80°-90°	3.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1064.9	65.3
0°-40°	1327.7	81.5
0°-60°	1595.8	97.9
0°-90°	1629.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1629.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4033	
5°	3677	317
15°	1493	428
25°	694	320
35°	419	263
45°	233	181
55°	96	87
65°	21	21
75°	9	10
85°	3	3
90°	0	



TEST NUMBER: P641070

CATALOG NUMBER: ML5612LSNFL2597FS1E - 691WB - 1200LM - 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4032.7
2.5°	3951.6
5°	3676.7
7.5°	3206.6
10°	2647.9
12.5°	2041.1
15°	1492.9
17.5°	1105.4
20°	889.1
22.5°	776.5
25°	693.9
27.5°	615.8
30°	543.7
32.5°	477.6
35°	419.0
37.5°	365.0
40°	315.4
42.5°	271.9
45°	232.8
47.5°	198.3
50°	166.7
52.5°	135.2
55°	96.1
57.5°	61.6
60°	33.0
62.5°	24.0
65°	21.0
67.5°	16.5
70°	13.5
72.5°	10.5
75°	9.0
77.5°	7.5
80°	6.0
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)