

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641109

Luminaire Tested: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641109  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K  
Description: ML56 RR, 25D TIR OPTIC, 6" SPECULAR CLEAR TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1338.3 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 0.37 / 0.37 / 0.39  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 13.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641109  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P641109

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94					94			
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	89					89			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83					83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78					78			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74					74			
6	91	82	77	73	89	82	76	73	80	76	72	79	75	72	78	74	71	70					70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66					66			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	64	63					63			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60					60			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58					58			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	240946
5°	209024
10°	136008
15°	73803
20°	44302
25°	35125
30°	28593
35°	22921
40°	18027
45°	13753
50°	7087
55°	1663
60°	954
65°	480
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13753 cd/sqm



TEST NUMBER: P641109

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	317.3	23.7
10°-20°	377.6	28.2
20°-30°	268.6	20.1
30°-40°	215.1	16.1
40°-50°	131.3	9.8
50°-60°	24.5	1.8
60°-70°	3.8	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	963.6	72.0
0°-40°	1178.7	88.1
0°-60°	1334.5	99.7
0°-90°	1338.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1338.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4395	
5°	3798	317
15°	1300	378
25°	581	269
35°	342	215
45°	177	131
55°	17	24
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641109

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692SC - 900LM - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4395.2
2.5°	4263.7
5°	3798.4
7.5°	3118.3
10°	2443.3
12.5°	1817.9
15°	1300.4
17.5°	955.5
20°	759.4
22.5°	656.4
25°	580.7
27.5°	513.7
30°	451.7
32.5°	395.8
35°	342.5
37.5°	295.3
40°	251.9
42.5°	214.7
45°	177.4
47.5°	127.8
50°	83.1
52.5°	37.2
55°	17.4
57.5°	11.2
60°	8.7
62.5°	6.2
65°	3.7
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)