

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640637

Luminaire Tested: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640637  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-31)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K  
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 971.7 lumens  
Efficiency: N/A  
Efficacy: 94.3 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct

Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640637  
CATALOG NUMBER: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P640637

CATALOG NUMBER: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88																			
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82																			
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77																			
5	94	86	80	76	92	85	80	76	83	79	75	81	77	74	80	76	74	72																			
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68																			
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64																			
8	81	72	67	63	80	72	66	63	71	66	62	70	65	62	69	65	62	61																			
9	78	69	63	59	77	68	63	59	67	62	59	66	62	59	66	62	59	57																			
10	75	65	60	56	74	65	60	56	64	59	56	63	59	56	63	59	56	54																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	128666
5°	124585
10°	108423
15°	89089
20°	69457
25°	52888
30°	38202
35°	26049
40°	16138
45°	9087
50°	3328
55°	1927
60°	1105
65°	318
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9087 cd/sqm



TEST NUMBER: P640637

CATALOG NUMBER: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	142.8	14.7
10°-20°	301.3	31.0
20°-30°	277.8	28.6
30°-40°	170.9	17.6
40°-50°	63.4	6.5
50°-60°	13.3	1.4
60°-70°	2.3	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.9	74.3
0°-40°	892.7	91.9
0°-60°	969.4	99.8
0°-90°	971.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	971.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1630	
5°	1572	143
15°	1090	301
25°	607	278
35°	270	171
45°	81	63
55°	14	13
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P640637

CATALOG NUMBER: ML5612LSFL4097FS1E - 593TBZB - 600LM - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1629.9
2.5°	1618.6
5°	1572.2
7.5°	1476.8
10°	1352.6
12.5°	1224.0
15°	1090.1
17.5°	955.4
20°	826.8
22.5°	709.5
25°	607.2
27.5°	508.3
30°	419.1
32.5°	339.5
35°	270.3
37.5°	210.8
40°	156.6
42.5°	118.1
45°	81.4
47.5°	43.7
50°	27.1
52.5°	19.2
55°	14.0
57.5°	9.6
60°	7.0
62.5°	4.4
65°	1.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)