

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641124

Luminaire Tested: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P641124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K
Description: ML56 RR, 25D TIR OPTIC, 6" WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1327.1 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.44
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P641124

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P641124

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	105	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	81																			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																			
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	65	72	68	64	71	67	64	62																			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	57	56																			
10	74	65	59	55	73	64	59	55	63	58	55	63	58	55	62	58	55	54																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184152
5°	168071
10°	123283
15°	70659
20°	43550
25°	35403
30°	29277
35°	23898
40°	19164
45°	14901
50°	8247
55°	3202
60°	2588
65°	2257
70°	1988
75°	2097
80°	1957
85°	1572

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14901 cd/sqm



TEST NUMBER: P641124

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	264.2	19.9
10°-20°	358.0	27.0
20°-30°	269.9	20.3
30°-40°	223.8	16.9
40°-50°	142.7	10.8
50°-60°	38.0	2.9
60°-70°	17.6	1.3
70°-80°	10.0	0.8
80°-90°	2.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	892.2	67.2
0°-40°	1116.0	84.1
0°-60°	1296.7	97.7
0°-90°	1327.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1327.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3359	
5°	3054	264
15°	1245	358
25°	585	270
35°	357	224
45°	192	143
55°	34	38
65°	17	18
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P641124

CATALOG NUMBER: ML5612LSNFL2597FS1E - 692W - 900LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3359.2
2.5°	3289.8
5°	3054.2
7.5°	2674.7
10°	2214.7
12.5°	1703.8
15°	1245.0
17.5°	928.8
20°	746.5
22.5°	654.7
25°	585.3
27.5°	520.8
30°	462.5
32.5°	408.0
35°	357.1
37.5°	310.0
40°	267.8
42.5°	229.4
45°	192.2
47.5°	142.6
50°	96.7
52.5°	50.8
55°	33.5
57.5°	27.3
60°	23.6
62.5°	21.1
65°	17.4
67.5°	14.9
70°	12.4
72.5°	11.2
75°	9.9
77.5°	7.4
80°	6.2
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)