

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640666

Luminaire Tested: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P640666  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-33)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K  
Description: ML56 RR, 40D TIR OPTIC, 5" SATIN NICKLE GIMBAL TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 976.2 lumens  
Efficiency: N/A  
Efficacy: 94.8 lumens/watt  
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69  
Luminous Opening: Circular (Dia: 0.42' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P640666

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P640666

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124932
5°	121027
10°	105329
15°	86482
20°	67685
25°	51233
30°	36799
35°	24979
40°	16117
45°	10438
50°	6055
55°	3386
60°	2273
65°	1588
70°	1177
75°	1037
80°	773
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10438 cd/sqm



TEST NUMBER: P640666

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	138.7	14.2
10°-20°	292.6	30.0
20°-30°	269.3	27.6
30°-40°	164.7	16.9
40°-50°	73.6	7.5
50°-60°	24.4	2.5
60°-70°	9.1	0.9
70°-80°	3.3	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	700.6	71.8
0°-40°	865.3	88.6
0°-60°	963.3	98.7
0°-90°	976.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	976.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1583	
5°	1527	139
15°	1058	293
25°	588	269
35°	259	165
45°	94	74
55°	25	24
65°	8	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P640666

CATALOG NUMBER: ML5612LSFL4097FS1E - 594SNB - 600LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1582.6
2.5°	1573.2
5°	1527.3
7.5°	1433.9
10°	1314.0
12.5°	1185.7
15°	1058.2
17.5°	929.0
20°	805.7
22.5°	690.2
25°	588.2
27.5°	491.3
30°	403.7
32.5°	325.5
35°	259.2
37.5°	203.1
40°	156.4
42.5°	120.7
45°	93.5
47.5°	68.8
50°	49.3
52.5°	34.8
55°	24.6
57.5°	18.7
60°	14.4
62.5°	11.9
65°	8.5
67.5°	6.8
70°	5.1
72.5°	4.2
75°	3.4
77.5°	1.7
80°	1.7
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)