

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P641126

Luminaire Tested: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K

Issue Date: 2/17/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P641126  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/17/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K  
Description: ML56 RR, 25D TIR OPTIC, 6" BLACK BAFFLE TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1318.8 lumens  
Efficiency: N/A  
Efficacy: 79.9 lumens/watt  
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.43  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P641126  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P641126

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88			
3	103	97	92	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82			
4	98	91	86	82	97	90	85	82	88	84	81	86	83	80	84	81	79	77			
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73			
6	90	81	76	72	88	80	75	71	79	74	71	78	74	70	76	73	70	69			
7	86	77	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65			
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62			
9	79	70	64	60	78	69	64	60	68	64	60	67	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	57	65	61	57	65	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	193872
5°	176871
10°	129328
15°	73582
20°	44792
25°	36292
30°	29783
35°	24059
40°	19007
45°	14443
50°	7326
55°	1644
60°	1020
65°	519
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14443 cd/sqm



TEST NUMBER: P641126

CATALOG NUMBER: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	277.7	21.1
10°-20°	372.5	28.2
20°-30°	276.3	21.0
30°-40°	225.5	17.1
40°-50°	137.8	10.4
50°-60°	24.9	1.9
60°-70°	4.0	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	926.5	70.3
0°-40°	1152.0	87.4
0°-60°	1314.7	99.7
0°-90°	1318.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1318.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3536	
5°	3214	278
15°	1296	373
25°	600	276
35°	360	225
45°	186	138
55°	17	25
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P641126  
CATALOG NUMBER: ML5612LSNFL2597FS1E - 693BB - 1200LM - 2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3536.5
2.5°	3465.2
5°	3214.1
7.5°	2808.3
10°	2323.3
12.5°	1782.8
15°	1296.5
17.5°	956.8
20°	767.8
22.5°	670.0
25°	600.0
27.5°	532.6
30°	470.5
32.5°	413.7
35°	359.5
37.5°	310.6
40°	265.6
42.5°	226.0
45°	186.3
47.5°	133.5
50°	85.9
52.5°	37.0
55°	17.2
57.5°	11.9
60°	9.3
62.5°	6.6
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)