

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640679

Luminaire Tested: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1717.6 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640679
CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P640679

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219835
5°	212948
10°	185319
15°	152263
20°	118803
25°	90229
30°	65001
35°	43838
40°	28308
45°	18264
50°	10697
55°	5987
60°	4026
65°	2802
70°	2077
75°	1830
80°	682
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18264 cd/sqm



TEST NUMBER: P640679

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.2	14.2
10°-20°	514.8	30.0
20°-30°	474.1	27.6
30°-40°	289.8	16.9
40°-50°	129.6	7.5
50°-60°	42.7	2.5
60°-70°	16.1	0.9
70°-80°	5.7	0.3
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1233.1	71.8
0°-40°	1522.9	88.7
0°-60°	1695.2	98.7
0°-90°	1717.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1717.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2785	
5°	2687	244
15°	1863	515
25°	1036	474
35°	455	290
45°	164	130
55°	44	43
65°	15	16
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P640679

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 1200LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2784.8
2.5°	2766.8
5°	2687.3
7.5°	2526.6
10°	2311.9
12.5°	2086.8
15°	1863.1
17.5°	1634.9
20°	1414.2
22.5°	1213.0
25°	1035.9
27.5°	866.2
30°	713.1
32.5°	573.5
35°	454.9
37.5°	357.3
40°	274.7
42.5°	213.2
45°	163.6
47.5°	121.6
50°	87.1
52.5°	61.6
55°	43.5
57.5°	31.5
60°	25.5
62.5°	21.0
65°	15.0
67.5°	12.0
70°	9.0
72.5°	7.5
75°	6.0
77.5°	3.0
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)