

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640684

Luminaire Tested: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-34)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K
Description: ML56 RR, 40D TIR OPTIC, 5" TUSCON BRONZE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1106.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 10.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640684
CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P640684

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81																			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	58	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	55	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141549
5°	137113
10°	119324
15°	98038
20°	76497
25°	58097
30°	41848
35°	28226
40°	18230
45°	11767
50°	6890
55°	3854
60°	2589
65°	1812
70°	1339
75°	1190
80°	455
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11767 cd/sqm



TEST NUMBER: P640684

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.2	14.2
10°-20°	331.5	30.0
20°-30°	305.3	27.6
30°-40°	186.6	16.9
40°-50°	83.4	7.5
50°-60°	27.5	2.5
60°-70°	10.4	0.9
70°-80°	3.7	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.0	71.8
0°-40°	980.6	88.7
0°-60°	1091.5	98.7
0°-90°	1106.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1106.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1793	
5°	1730	157
15°	1200	331
25°	667	305
35°	293	187
45°	105	83
55°	28	28
65°	10	10
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P640684

CATALOG NUMBER: ML5612LSFL4097FS1E - 594TBZB - 600LM - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1793.1
2.5°	1781.5
5°	1730.3
7.5°	1626.8
10°	1488.6
12.5°	1343.6
15°	1199.6
17.5°	1052.7
20°	910.6
22.5°	781.0
25°	667.0
27.5°	557.7
30°	459.1
32.5°	369.3
35°	292.9
37.5°	230.1
40°	176.9
42.5°	137.3
45°	105.4
47.5°	78.3
50°	56.1
52.5°	39.6
55°	28.0
57.5°	20.3
60°	16.4
62.5°	13.5
65°	9.7
67.5°	7.7
70°	5.8
72.5°	4.8
75°	3.9
77.5°	1.9
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)