

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P640693

Luminaire Tested: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K

Issue Date: 2/17/2023

Test Information

Test Method: LM-79-2019
Report Number: P640693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2212-866-32)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/17/2023
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K
Description: ML56 RR, 40D TIR OPTIC, 5" WHITE GIMBAL TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1603.4 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.69
Luminous Opening: Circular (Dia: 0.42' x H: 0')
CIE Type: Direct

Input Watts (W): 16.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P640693
CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P640693

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	86	84	87	85	83	81																			
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																			
6	88	79	74	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66																			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																			
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205254
5°	198732
10°	172838
15°	142113
20°	111032
25°	84123
30°	60298
35°	41024
40°	26463
45°	16980
50°	9935
55°	5574
60°	3742
65°	2615
70°	2262
75°	1708
80°	1273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16980 cd/sqm



TEST NUMBER: P640693

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	227.7	14.2
10°-20°	480.4	30.0
20°-30°	442.1	27.6
30°-40°	270.4	16.9
40°-50°	120.8	7.5
50°-60°	40.1	2.5
60°-70°	15.2	0.9
70°-80°	6.1	0.4
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1150.2	71.7
0°-40°	1420.5	88.6
0°-60°	1581.4	98.6
0°-90°	1603.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1603.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2600	
5°	2508	228
15°	1739	480
25°	966	442
35°	426	270
45°	152	121
55°	40	40
65°	14	15
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P640693

CATALOG NUMBER: ML5612LSFL4097FS1E - 594WB - 1200LM - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2600.1
2.5°	2583.3
5°	2507.9
7.5°	2353.0
10°	2156.2
12.5°	1948.3
15°	1738.9
17.5°	1524.0
20°	1321.7
22.5°	1133.2
25°	965.8
27.5°	806.7
30°	661.5
32.5°	534.5
35°	425.7
37.5°	333.6
40°	256.8
42.5°	199.6
45°	152.1
47.5°	113.0
50°	80.9
52.5°	57.2
55°	40.5
57.5°	30.7
60°	23.7
62.5°	19.5
65°	14.0
67.5°	11.2
70°	9.8
72.5°	7.0
75°	5.6
77.5°	4.2
80°	2.8
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)